

O-RING



Profile	ID	OD	THK	Material
O-Ring	1.42	4.46	1.52	NBR
O-Ring	1.78	5.34	1.78	NBR
O-Ring	2	5	1.5	NBR
O-Ring	2	6	2	NBR
O-Ring	2.06	7.3	2.62	NBR
O-Ring	2.4	5.8	1.7	NBR
O-Ring	2.5	5.5	1.5	NBR
O-Ring	2.5	6.5	2	NBR
O-Ring	2.57	6.13	1.78	NBR
O-Ring	2.84	8.08	2.62	NBR
O-Ring	2.9	6.46	1.78	NBR
O-Ring	3	5	1	NBR
O-Ring	3	6	1.5	NBR
O-Ring	3	7	2	NBR
O-Ring	3	8	2.5	NBR
O-Ring	3	9	3	NBR
O-Ring	3.5	5.5	1	NBR
O-Ring	3.5	6.5	1.5	NBR
O-Ring	3.5	7.5	2	NBR
O-Ring	3.5	8.5	2.5	NBR
O-Ring	3.63	8.87	2.62	NBR
O-Ring	3.68	7.24	1.78	NBR
O-Ring	4	6	1	NBR
O-Ring	4	6.4	1.2	NBR
O-Ring	4	7	1.5	NBR
O-Ring	4	7.4	1.7	NBR
O-Ring	4	7.6	1.8	NBR
O-Ring	4	8	2	NBR
O-Ring	4	9	2.5	NBR
O-Ring	4	10	3	NBR
O-Ring	4	14	5	NBR
O-Ring	4.34	11.4	3.53	NBR
O-Ring	4.42	9.66	2.62	NBR
O-Ring	4.47	8.03	1.78	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	4.5	7.5	1.5	NBR
O-Ring	4.5	8.5	2	NBR
O-Ring	4.7	8.1	1.7	NBR
O-Ring	4.8	8.6	1.9	NBR
O-Ring	5	8	1.5	NBR
O-Ring	5	8.56	1.78	NBR
O-Ring	5	9	2	NBR
O-Ring	5	10	2.5	NBR
O-Ring	5	11	3	NBR
O-Ring	5.23	10.47	2.62	NBR
O-Ring	5.28	8.84	1.78	NBR
O-Ring	5.3	9.8	2.25	NBR
O-Ring	5.3	10.1	2.4	NBR
O-Ring	5.5	8.5	1.5	NBR
O-Ring	5.5	9.5	2	NBR
O-Ring	5.6	8	1.2	NBR
O-Ring	5.6	10.4	2.4	NBR
O-Ring	5.94	13	3.53	NBR
O-Ring	6	8	1	NBR
O-Ring	6	8.5	1.25	NBR
O-Ring	6	9	1.5	NBR
O-Ring	6	10	2	NBR
O-Ring	6	10.4	2.2	NBR
O-Ring	6	11	2.5	NBR
O-Ring	6	12	3	NBR
O-Ring	6	14	4	NBR
O-Ring	6.02	11.26	2.62	NBR
O-Ring	6.07	9.63	1.78	NBR
O-Ring	6.3	9.9	1.8	NBR
O-Ring	6.5	9.5	1.5	NBR
O-Ring	6.5	10.5	2	NBR
O-Ring	6.75	10.31	1.78	NBR
O-Ring	7	9	1	NBR
O-Ring	7	10	1.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	7	10.56	1.78	NBR
O-Ring	7	11	2	NBR
O-Ring	7	12	2.5	NBR
O-Ring	7	13	3	NBR
O-Ring	7	15	4	NBR
O-Ring	7.1	10.3	1.6	NBR
O-Ring	7.2	11	1.9	NBR
O-Ring	7.2	11.2	2	NBR
O-Ring	7.2	13.6	3.2	NBR
O-Ring	7.4	12	2.3	NBR
O-Ring	7.5	10.5	1.5	NBR
O-Ring	7.5	11	1.75	NBR
O-Ring	7.5	11.2	2	NBR
O-Ring	7.5	11.5	2	NBR
O-Ring	7.52	14.58	3.53	NBR
O-Ring	7.59	12.83	2.62	NBR
O-Ring	7.6	12.4	2.4	NBR
O-Ring	7.6	12.6	2.5	NBR
O-Ring	7.65	11.21	1.78	NBR
O-Ring	7.65	11.21	1.78	NBR
O-Ring	8	10	1	NBR
O-Ring	8	10.5	1.25	NBR
O-Ring	8	11	1.5	NBR
O-Ring	8	11.6	1.8	NBR
O-Ring	8	11.8	1.9	NBR
O-Ring	8	12	2	NBR
O-Ring	8	12.4	2.2	NBR
O-Ring	8	13	2.5	NBR
O-Ring	8	14	3	NBR
O-Ring	8	15	3.5	NBR
O-Ring	8	16	4	NBR
O-Ring	8.4	12	1.8	NBR
O-Ring	8.5	11.5	1.5	NBR
O-Ring	8.5	12.5	2	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	8.5	13.5	2.5	NBR
O-Ring	8.5	13.9	2.7	NBR
O-Ring	8.5	14.9	3.2	NBR
O-Ring	8.73	12.29	1.78	NBR
O-Ring	8.8	12.6	1.9	NBR
O-Ring	9	11	1	NBR
O-Ring	9	12	1.5	NBR
O-Ring	9	12	1.5	NBR
O-Ring	9	12.6	1.8	NBR
O-Ring	9	13	2	NBR
O-Ring	9	14	2.5	NBR
O-Ring	9	15	3	NBR
O-Ring	9	16	3.5	NBR
O-Ring	9	17	4	NBR
O-Ring	9.12	16.18	3.53	NBR
O-Ring	9.19	14.43	2.62	NBR
O-Ring	9.25	12.81	1.78	NBR
O-Ring	9.25	12.81	1.78	NBR
O-Ring	9.3	13.7	2.2	NBR
O-Ring	9.3	14.1	2.4	NBR
O-Ring	9.5	12.5	1.5	NBR
O-Ring	9.5	13.1	1.8	NBR
O-Ring	9.5	13.5	2	NBR
O-Ring	9.5	14.5	2.5	NBR
O-Ring	9.5	15.5	3	NBR
O-Ring	9.75	13.31	1.78	NBR
O-Ring	9.8	14.6	2.4	NBR
O-Ring	10	12	1	NBR
O-Ring	10	13	1.5	NBR
O-Ring	10	14	2	NBR
O-Ring	10	14	2	NBR
O-Ring	10	14.4	2.2	NBR
O-Ring	10	15	2.5	NBR
O-Ring	10	16	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	10	17	3.5	NBR
O-Ring	10	18	4	NBR
O-Ring	10.5	14.1	1.8	NBR
O-Ring	10.5	14.5	2	NBR
O-Ring	10.5	15.1	2.3	NBR
O-Ring	10.5	15.5	2.5	NBR
O-Ring	10.69	17.75	3.53	NBR
O-Ring	10.77	16.01	2.62	NBR
O-Ring	10.8	15.6	2.4	NBR
O-Ring	10.82	14.38	1.78	NBR
O-Ring	10.82	14.38	1.78	NBR
O-Ring	11	13	1	NBR
O-Ring	11	14	1.5	NBR
O-Ring	11	14.6	1.8	NBR
O-Ring	11	15	2	NBR
O-Ring	11	16	2.5	NBR
O-Ring	11	16	2.5	NBR
O-Ring	11	17	3	NBR
O-Ring	11	18	3.5	NBR
O-Ring	11	19	4	NBR
O-Ring	11.11	15.87	2.38	NBR
O-Ring	11.5	14.5	1.5	NBR
O-Ring	11.5	15.5	2	NBR
O-Ring	11.5	16.5	2.5	NBR
O-Ring	11.5	17.5	3	NBR
O-Ring	11.5	20.1	4.3	NBR
O-Ring	11.6	16.2	2.3	NBR
O-Ring	11.8	16.6	2.4	NBR
O-Ring	11.91	17.15	2.62	NBR
O-Ring	12	14	1	NBR
O-Ring	12	15	1.5	NBR
O-Ring	12	15.6	1.8	NBR
O-Ring	12	16	2	NBR
O-Ring	12	16	2	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	12	16	2	NBR
O-Ring	12	16.4	2.2	NBR
O-Ring	12	17	2.5	NBR
O-Ring	12	18	3	NBR
O-Ring	12	19	3.5	NBR
O-Ring	12	20	4	NBR
O-Ring	12.29	19.35	3.53	NBR
O-Ring	12.37	17.61	2.62	NBR
O-Ring	12.42	15.98	1.78	NBR
O-Ring	12.42	15.98	1.78	NBR
O-Ring	12.5	15.5	1.5	NBR
O-Ring	12.5	16.5	2	NBR
O-Ring	12.5	17.5	2.5	NBR
O-Ring	12.5	19.5	3.5	NBR
O-Ring	12.7	15.9	1.6	NBR
O-Ring	12.7	18.9	3.1	NBR
O-Ring	13	15	1	NBR
O-Ring	13	16	1.5	NBR
O-Ring	13	17	2	NBR
O-Ring	13	18	2.5	NBR
O-Ring	13	19	3	NBR
O-Ring	13	20	3.5	NBR
O-Ring	13	21	4	NBR
O-Ring	13.1	18.34	2.62	NBR
O-Ring	13.5	16.5	1.5	NBR
O-Ring	13.5	17.5	2	NBR
O-Ring	13.5	18.5	2.5	NBR
O-Ring	13.5	21.5	4	NBR
O-Ring	13.6	19	2.7	NBR
O-Ring	13.64	24.3	5.33	NBR
O-Ring	13.8	18.6	2.4	NBR
O-Ring	13.87	20.93	3.53	NBR
O-Ring	13.94	19.18	2.62	NBR
O-Ring	14	16	1	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	14	17	1.5	NBR
O-Ring	14	17.4	1.7	NBR
O-Ring	14	17.56	1.78	NBR
O-Ring	14	18	2	NBR
O-Ring	14	19	2.5	NBR
O-Ring	14	20	3	NBR
O-Ring	14	22	4	NBR
O-Ring	14.1	17.3	1.6	NBR
O-Ring	14.5	17.5	1.5	NBR
O-Ring	14.5	18.5	2	NBR
O-Ring	14.5	19.5	2.5	NBR
O-Ring	14.5	20.5	3	NBR
O-Ring	14.5	21.5	3.5	NBR
O-Ring	15	17	1	NBR
O-Ring	15	18	1.5	NBR
O-Ring	15	18.56	1.78	NBR
O-Ring	15	19	2	NBR
O-Ring	15	20	2.5	NBR
O-Ring	15	20	2.5	NBR
O-Ring	15	21	3	NBR
O-Ring	15	22	3.5	NBR
O-Ring	15	23	4	NBR
O-Ring	15	25	5	NBR
O-Ring	15.08	20.32	2.62	NBR
O-Ring	15.3	20.1	2.4	NBR
O-Ring	15.47	22.53	3.53	NBR
O-Ring	15.5	19.5	2	NBR
O-Ring	15.5	21.5	3	NBR
O-Ring	15.54	20.78	2.62	NBR
O-Ring	15.54	20.78	2.62	NBR
O-Ring	15.6	19.16	1.78	NBR
O-Ring	15.6	20.2	2.3	NBR
O-Ring	16	18	1	NBR
O-Ring	16	19	1.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	16	19.4	1.7	NBR
O-Ring	16	20	2	NBR
O-Ring	16	21	2.5	NBR
O-Ring	16	22	3	NBR
O-Ring	16	23	3.5	NBR
O-Ring	16	24	4	NBR
O-Ring	16	26	5	NBR
O-Ring	16.3	21.1	2.4	NBR
O-Ring	16.3	21.1	2.4	NBR
O-Ring	16.35	20.75	2.2	NBR
O-Ring	16.5	20.5	2	NBR
O-Ring	16.5	21.5	2.5	NBR
O-Ring	16.5	22.5	3	NBR
O-Ring	16.82	27.48	5.33	NBR
O-Ring	17	19	1	NBR
O-Ring	17	20	1.5	NBR
O-Ring	17	21	2	NBR
O-Ring	17	22	2.5	NBR
O-Ring	17	23	3	NBR
O-Ring	17	25	4	NBR
O-Ring	17	27	5	NBR
O-Ring	17.04	24.1	3.53	NBR
O-Ring	17.1	20.3	1.6	NBR
O-Ring	17.12	22.36	2.62	NBR
O-Ring	17.17	20.73	1.78	NBR
O-Ring	17.3	22.1	2.4	NBR
O-Ring	17.5	21.5	2	NBR
O-Ring	17.5	22.5	2.5	NBR
O-Ring	17.5	23.5	3	NBR
O-Ring	17.55	22.05	2.25	NBR
O-Ring	17.8	22.6	2.4	NBR
O-Ring	17.96	23.2	2.62	NBR
O-Ring	18	20	1	NBR
O-Ring	18	21	1.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	18	21.6	1.8	NBR
O-Ring	18	22	2	NBR
O-Ring	18	23	2.5	NBR
O-Ring	18	24	3	NBR
O-Ring	18	25	3.5	NBR
O-Ring	18	26	4	NBR
O-Ring	18	28	5	NBR
O-Ring	18.3	23.1	2.4	NBR
O-Ring	18.42	29.08	5.33	NBR
O-Ring	18.5	21.5	1.5	NBR
O-Ring	18.5	23.5	2.5	NBR
O-Ring	18.5	24.5	3	NBR
O-Ring	18.64	25.7	3.53	NBR
O-Ring	18.64	25.7	3.53	NBR
O-Ring	18.72	23.96	2.62	NBR
O-Ring	18.77	22.33	1.78	NBR
O-Ring	18.77	22.33	1.78	NBR
O-Ring	19	22	1.5	NBR
O-Ring	19	22.6	1.8	NBR
O-Ring	19	23	2	NBR
O-Ring	19	24	2.5	NBR
O-Ring	19	24.5	2.75	NBR
O-Ring	19	25	3	NBR
O-Ring	19	26	3.5	NBR
O-Ring	19	27	4	NBR
O-Ring	19	29	5	NBR
O-Ring	19.05	25.39	3.17	NBR
O-Ring	19.5	24.5	2.5	NBR
O-Ring	19.5	25.5	3	NBR
O-Ring	19.99	30.65	5.33	NBR
O-Ring	20	22	1	NBR
O-Ring	20	23	1.5	NBR
O-Ring	20	24.4	2.2	NBR
O-Ring	20	25	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	20	26	3	NBR
O-Ring	20	27	3.5	NBR
O-Ring	20	28	4	NBR
O-Ring	20	30	5	NBR
O-Ring	1.42	4.46	1.52	NBR
O-Ring	1.78	5.34	1.78	NBR
O-Ring	2	5	1.5	NBR
O-Ring	2	6	2	NBR
O-Ring	2.06	7.3	2.62	NBR
O-Ring	2.4	5.8	1.7	NBR
O-Ring	2.5	5.5	1.5	NBR
O-Ring	2.5	6.5	2	NBR
O-Ring	2.57	6.13	1.78	NBR
O-Ring	2.84	8.08	2.62	NBR
O-Ring	2.9	6.46	1.78	NBR
O-Ring	3	5	1	NBR
O-Ring	3	6	1.5	NBR
O-Ring	3	7	2	NBR
O-Ring	3	8	2.5	NBR
O-Ring	3	9	3	NBR
O-Ring	3.5	5.5	1	NBR
O-Ring	3.5	6.5	1.5	NBR
O-Ring	3.5	7.5	2	NBR
O-Ring	3.5	8.5	2.5	NBR
O-Ring	3.63	8.87	2.62	NBR
O-Ring	3.68	7.24	1.78	NBR
O-Ring	4	6	1	NBR
O-Ring	4	6.4	1.2	NBR
O-Ring	4	7	1.5	NBR
O-Ring	4	7.4	1.7	NBR
O-Ring	4	7.6	1.8	NBR
O-Ring	4	8	2	NBR
O-Ring	4	9	2.5	NBR
O-Ring	4	10	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	4	14	5	NBR
O-Ring	4.34	11.4	3.53	NBR
O-Ring	4.42	9.66	2.62	NBR
O-Ring	4.47	8.03	1.78	NBR
O-Ring	4.5	7.5	1.5	NBR
O-Ring	4.5	8.5	2	NBR
O-Ring	4.7	8.1	1.7	NBR
O-Ring	4.8	8.6	1.9	NBR
O-Ring	5	8	1.5	NBR
O-Ring	5	8.56	1.78	NBR
O-Ring	5	9	2	NBR
O-Ring	5	10	2.5	NBR
O-Ring	5	11	3	NBR
O-Ring	5.23	10.47	2.62	NBR
O-Ring	5.28	8.84	1.78	NBR
O-Ring	5.3	9.8	2.25	NBR
O-Ring	5.3	10.1	2.4	NBR
O-Ring	5.5	8.5	1.5	NBR
O-Ring	5.5	9.5	2	NBR
O-Ring	5.6	8	1.2	NBR
O-Ring	5.6	10.4	2.4	NBR
O-Ring	5.94	13	3.53	NBR
O-Ring	6	8	1	NBR
O-Ring	6	8.5	1.25	NBR
O-Ring	6	9	1.5	NBR
O-Ring	6	10	2	NBR
O-Ring	6	10.4	2.2	NBR
O-Ring	6	11	2.5	NBR
O-Ring	6	12	3	NBR
O-Ring	6	14	4	NBR
O-Ring	6.02	11.26	2.62	NBR
O-Ring	6.07	9.63	1.78	NBR
O-Ring	6.3	9.9	1.8	NBR
O-Ring	6.5	9.5	1.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	6.5	10.5	2	NBR
O-Ring	6.75	10.31	1.78	NBR
O-Ring	7	9	1	NBR
O-Ring	7	10	1.5	NBR
O-Ring	7	10.56	1.78	NBR
O-Ring	7	11	2	NBR
O-Ring	7	12	2.5	NBR
O-Ring	7	13	3	NBR
O-Ring	7	15	4	NBR
O-Ring	7.1	10.3	1.6	NBR
O-Ring	7.2	11	1.9	NBR
O-Ring	7.2	11.2	2	NBR
O-Ring	7.2	13.6	3.2	NBR
O-Ring	7.4	12	2.3	NBR
O-Ring	7.5	10.5	1.5	NBR
O-Ring	7.5	11	1.75	NBR
O-Ring	7.5	11.2	2	NBR
O-Ring	7.5	11.5	2	NBR
O-Ring	7.52	14.58	3.53	NBR
O-Ring	7.59	12.83	2.62	NBR
O-Ring	7.6	12.4	2.4	NBR
O-Ring	7.6	12.6	2.5	NBR
O-Ring	7.65	11.21	1.78	NBR
O-Ring	7.65	11.21	1.78	NBR
O-Ring	8	10	1	NBR
O-Ring	8	10.5	1.25	NBR
O-Ring	8	11	1.5	NBR
O-Ring	8	11.6	1.8	NBR
O-Ring	8	11.8	1.9	NBR
O-Ring	8	12	2	NBR
O-Ring	8	12.4	2.2	NBR
O-Ring	8	13	2.5	NBR
O-Ring	8	14	3	NBR
O-Ring	8	15	3.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	8	16	4	NBR
O-Ring	8.4	12	1.8	NBR
O-Ring	8.5	11.5	1.5	NBR
O-Ring	8.5	12.5	2	NBR
O-Ring	8.5	13.5	2.5	NBR
O-Ring	8.5	13.9	2.7	NBR
O-Ring	8.5	14.9	3.2	NBR
O-Ring	8.73	12.29	1.78	NBR
O-Ring	8.8	12.6	1.9	NBR
O-Ring	9	11	1	NBR
O-Ring	9	12	1.5	NBR
O-Ring	9	12	1.5	NBR
O-Ring	9	12.6	1.8	NBR
O-Ring	9	13	2	NBR
O-Ring	9	14	2.5	NBR
O-Ring	9	15	3	NBR
O-Ring	9	16	3.5	NBR
O-Ring	9	17	4	NBR
O-Ring	9.12	16.18	3.53	NBR
O-Ring	9.19	14.43	2.62	NBR
O-Ring	9.25	12.81	1.78	NBR
O-Ring	9.25	12.81	1.78	NBR
O-Ring	9.3	13.7	2.2	NBR
O-Ring	9.3	14.1	2.4	NBR
O-Ring	9.5	12.5	1.5	NBR
O-Ring	9.5	13.1	1.8	NBR
O-Ring	9.5	13.5	2	NBR
O-Ring	9.5	14.5	2.5	NBR
O-Ring	9.5	15.5	3	NBR
O-Ring	9.75	13.31	1.78	NBR
O-Ring	9.8	14.6	2.4	NBR
O-Ring	10	12	1	NBR
O-Ring	10	13	1.5	NBR
O-Ring	10	14	2	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	10	14	2	NBR
O-Ring	10	14.4	2.2	NBR
O-Ring	10	15	2.5	NBR
O-Ring	10	16	3	NBR
O-Ring	10	17	3.5	NBR
O-Ring	10	18	4	NBR
O-Ring	10.5	14.1	1.8	NBR
O-Ring	10.5	14.5	2	NBR
O-Ring	10.5	15.1	2.3	NBR
O-Ring	10.5	15.5	2.5	NBR
O-Ring	10.69	17.75	3.53	NBR
O-Ring	10.77	16.01	2.62	NBR
O-Ring	10.8	15.6	2.4	NBR
O-Ring	10.82	14.38	1.78	NBR
O-Ring	10.82	14.38	1.78	NBR
O-Ring	11	13	1	NBR
O-Ring	11	14	1.5	NBR
O-Ring	11	14.6	1.8	NBR
O-Ring	11	15	2	NBR
O-Ring	11	16	2.5	NBR
O-Ring	11	16	2.5	NBR
O-Ring	11	17	3	NBR
O-Ring	11	18	3.5	NBR
O-Ring	11	19	4	NBR
O-Ring	11.11	15.87	2.38	NBR
O-Ring	11.5	14.5	1.5	NBR
O-Ring	11.5	15.5	2	NBR
O-Ring	11.5	16.5	2.5	NBR
O-Ring	11.5	17.5	3	NBR
O-Ring	11.5	20.1	4.3	NBR
O-Ring	11.6	16.2	2.3	NBR
O-Ring	11.8	16.6	2.4	NBR
O-Ring	11.91	17.15	2.62	NBR
O-Ring	12	14	1	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	12	15	1.5	NBR
O-Ring	12	15.6	1.8	NBR
O-Ring	12	16	2	NBR
O-Ring	12	16	2	NBR
O-Ring	12	16	2	NBR
O-Ring	12	16.4	2.2	NBR
O-Ring	12	17	2.5	NBR
O-Ring	12	18	3	NBR
O-Ring	12	19	3.5	NBR
O-Ring	12	20	4	NBR
O-Ring	12.29	19.35	3.53	NBR
O-Ring	12.37	17.61	2.62	NBR
O-Ring	12.42	15.98	1.78	NBR
O-Ring	12.42	15.98	1.78	NBR
O-Ring	12.5	15.5	1.5	NBR
O-Ring	12.5	16.5	2	NBR
O-Ring	12.5	17.5	2.5	NBR
O-Ring	12.5	19.5	3.5	NBR
O-Ring	12.7	15.9	1.6	NBR
O-Ring	12.7	18.9	3.1	NBR
O-Ring	13	15	1	NBR
O-Ring	13	16	1.5	NBR
O-Ring	13	17	2	NBR
O-Ring	13	18	2.5	NBR
O-Ring	13	19	3	NBR
O-Ring	13	20	3.5	NBR
O-Ring	13	21	4	NBR
O-Ring	13.1	18.34	2.62	NBR
O-Ring	13.5	16.5	1.5	NBR
O-Ring	13.5	17.5	2	NBR
O-Ring	13.5	18.5	2.5	NBR
O-Ring	13.5	21.5	4	NBR
O-Ring	13.6	19	2.7	NBR
O-Ring	13.64	24.3	5.33	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	13.8	18.6	2.4	NBR
O-Ring	13.87	20.93	3.53	NBR
O-Ring	13.94	19.18	2.62	NBR
O-Ring	14	16	1	NBR
O-Ring	14	17	1.5	NBR
O-Ring	14	17.4	1.7	NBR
O-Ring	14	17.56	1.78	NBR
O-Ring	14	18	2	NBR
O-Ring	14	19	2.5	NBR
O-Ring	14	20	3	NBR
O-Ring	14	22	4	NBR
O-Ring	14.1	17.3	1.6	NBR
O-Ring	14.5	17.5	1.5	NBR
O-Ring	14.5	18.5	2	NBR
O-Ring	14.5	19.5	2.5	NBR
O-Ring	14.5	20.5	3	NBR
O-Ring	14.5	21.5	3.5	NBR
O-Ring	15	17	1	NBR
O-Ring	15	18	1.5	NBR
O-Ring	15	18.56	1.78	NBR
O-Ring	15	19	2	NBR
O-Ring	15	20	2.5	NBR
O-Ring	15	20	2.5	NBR
O-Ring	15	21	3	NBR
O-Ring	15	22	3.5	NBR
O-Ring	15	23	4	NBR
O-Ring	15	25	5	NBR
O-Ring	15.08	20.32	2.62	NBR
O-Ring	15.3	20.1	2.4	NBR
O-Ring	15.47	22.53	3.53	NBR
O-Ring	15.5	19.5	2	NBR
O-Ring	15.5	21.5	3	NBR
O-Ring	15.54	20.78	2.62	NBR
O-Ring	15.54	20.78	2.62	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	15.6	19.16	1.78	NBR
O-Ring	15.6	20.2	2.3	NBR
O-Ring	16	18	1	NBR
O-Ring	16	19	1.5	NBR
O-Ring	16	19.4	1.7	NBR
O-Ring	16	20	2	NBR
O-Ring	16	21	2.5	NBR
O-Ring	16	22	3	NBR
O-Ring	16	23	3.5	NBR
O-Ring	16	24	4	NBR
O-Ring	16	26	5	NBR
O-Ring	16.3	21.1	2.4	NBR
O-Ring	16.3	21.1	2.4	NBR
O-Ring	16.35	20.75	2.2	NBR
O-Ring	16.5	20.5	2	NBR
O-Ring	16.5	21.5	2.5	NBR
O-Ring	16.5	22.5	3	NBR
O-Ring	16.82	27.48	5.33	NBR
O-Ring	17	19	1	NBR
O-Ring	17	20	1.5	NBR
O-Ring	17	21	2	NBR
O-Ring	17	22	2.5	NBR
O-Ring	17	23	3	NBR
O-Ring	17	25	4	NBR
O-Ring	17	27	5	NBR
O-Ring	17.04	24.1	3.53	NBR
O-Ring	17.1	20.3	1.6	NBR
O-Ring	17.12	22.36	2.62	NBR
O-Ring	17.17	20.73	1.78	NBR
O-Ring	17.3	22.1	2.4	NBR
O-Ring	17.5	21.5	2	NBR
O-Ring	17.5	22.5	2.5	NBR
O-Ring	17.5	23.5	3	NBR
O-Ring	17.55	22.05	2.25	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	17.8	22.6	2.4	NBR
O-Ring	17.96	23.2	2.62	NBR
O-Ring	18	20	1	NBR
O-Ring	18	21	1.5	NBR
O-Ring	18	21.6	1.8	NBR
O-Ring	18	22	2	NBR
O-Ring	18	23	2.5	NBR
O-Ring	18	24	3	NBR
O-Ring	18	25	3.5	NBR
O-Ring	18	26	4	NBR
O-Ring	18	28	5	NBR
O-Ring	18.3	23.1	2.4	NBR
O-Ring	18.42	29.08	5.33	NBR
O-Ring	18.5	21.5	1.5	NBR
O-Ring	18.5	23.5	2.5	NBR
O-Ring	18.5	24.5	3	NBR
O-Ring	18.64	25.7	3.53	NBR
O-Ring	18.64	25.7	3.53	NBR
O-Ring	18.72	23.96	2.62	NBR
O-Ring	18.77	22.33	1.78	NBR
O-Ring	18.77	22.33	1.78	NBR
O-Ring	19	22	1.5	NBR
O-Ring	19	22.6	1.8	NBR
O-Ring	19	23	2	NBR
O-Ring	19	24	2.5	NBR
O-Ring	19	24.5	2.75	NBR
O-Ring	19	25	3	NBR
O-Ring	19	26	3.5	NBR
O-Ring	19	27	4	NBR
O-Ring	19	29	5	NBR
O-Ring	19.05	25.39	3.17	NBR
O-Ring	19.5	24.5	2.5	NBR
O-Ring	19.5	25.5	3	NBR
O-Ring	19.99	30.65	5.33	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	20	22	1	NBR
O-Ring	20	23	1.5	NBR
O-Ring	20	24.4	2.2	NBR
O-Ring	20	25	2.5	NBR
O-Ring	20	26	3	NBR
O-Ring	20	27	3.5	NBR
O-Ring	20	28	4	NBR
O-Ring	20	30	5	NBR
O-Ring	20.22	27.28	3.53	NBR
O-Ring	20.29	25.53	2.62	NBR
O-Ring	20.3	25.1	2.4	NBR
O-Ring	20.3	25.1	2.4	NBR
O-Ring	20.35	23.91	1.78	NBR
O-Ring	21	23	1	NBR
O-Ring	21	24	1.5	NBR
O-Ring	21	24.6	1.8	NBR
O-Ring	21	25	2	NBR
O-Ring	21	26	2.5	NBR
O-Ring	21	27	3	NBR
O-Ring	21	28	3.5	NBR
O-Ring	21	29	4	NBR
O-Ring	21	31	5	NBR
O-Ring	21	33	6	NBR
O-Ring	21.4	25.4	2	NBR
O-Ring	21.5	26.5	2.5	NBR
O-Ring	21.5	27.5	3	NBR
O-Ring	21.6	32.26	5.33	NBR
O-Ring	21.82	28.88	3.53	NBR
O-Ring	21.89	27.13	2.62	NBR
O-Ring	21.95	25.51	1.78	NBR
O-Ring	22	25	1.5	NBR
O-Ring	22	26	2	NBR
O-Ring	22	27	2.5	NBR
O-Ring	22	28	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	22	29	3.5	NBR
O-Ring	22	30	4	NBR
O-Ring	22	32	5	NBR
O-Ring	22.23	27.47	2.62	NBR
O-Ring	22.3	27.1	2.4	NBR
O-Ring	22.5	25.5	1.5	NBR
O-Ring	23	25	1	NBR
O-Ring	23	26	1.5	NBR
O-Ring	23	27	2	NBR
O-Ring	23	28	2.5	NBR
O-Ring	23	29	3	NBR
O-Ring	23	30	3.5	NBR
O-Ring	23	31	4	NBR
O-Ring	23	33	5	NBR
O-Ring	23.16	33.82	5.33	NBR
O-Ring	23.39	30.45	3.53	NBR
O-Ring	23.47	28.71	2.62	NBR
O-Ring	23.5	30.5	3.5	NBR
O-Ring	23.52	27.08	1.78	NBR
O-Ring	23.6	28.6	2.5	NBR
O-Ring	24	27	1.5	NBR
O-Ring	24	28	2	NBR
O-Ring	24	29	2.5	NBR
O-Ring	24	30	3	NBR
O-Ring	24	31	3.5	NBR
O-Ring	24	32	4	NBR
O-Ring	24	33	4.5	NBR
O-Ring	24	34	5	NBR
O-Ring	24.4	29.4	2.5	NBR
O-Ring	24.5	30.5	3	NBR
O-Ring	24.5	31.5	3.5	NBR
O-Ring	24.5	32.5	4	NBR
O-Ring	24.77	35.43	5.33	NBR
O-Ring	24.99	32.05	3.53	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	24.99	32.05	3.53	NBR
O-Ring	25	28	1.5	NBR
O-Ring	25	28.5	1.75	NBR
O-Ring	25	29	2	NBR
O-Ring	25	30	2.5	NBR
O-Ring	25	31	3	NBR
O-Ring	25	31.4	3.2	NBR
O-Ring	25	33	4	NBR
O-Ring	25	35	5	NBR
O-Ring	25	36	5.5	NBR
O-Ring	25	37	6	NBR
O-Ring	25.07	30.31	2.62	NBR
O-Ring	25.12	28.68	1.78	NBR
O-Ring	25.3	30.1	2.4	NBR
O-Ring	25.3	30.1	2.4	NBR
O-Ring	25.5	31.5	3	NBR
O-Ring	25.8	32.86	3.53	NBR
O-Ring	26	28	1	NBR
O-Ring	26	29	1.5	NBR
O-Ring	26	30	2	NBR
O-Ring	26	31	2.5	NBR
O-Ring	26	32	3	NBR
O-Ring	26	33	3.5	NBR
O-Ring	26	34	4	NBR
O-Ring	26	35	4.5	NBR
O-Ring	26	36	5	NBR
O-Ring	26.34	37	5.33	NBR
O-Ring	26.5	32.5	3	NBR
O-Ring	26.57	33.63	3.53	NBR
O-Ring	26.64	31.88	2.62	NBR
O-Ring	26.7	30.26	1.78	NBR
O-Ring	27	30	1.5	NBR
O-Ring	27	31	2	NBR
O-Ring	27	32	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	27	33	3	NBR
O-Ring	27	34	3.5	NBR
O-Ring	27	35	4	NBR
O-Ring	27	37	5	NBR
O-Ring	27.5	33.5	3	NBR
O-Ring	27.94	38.6	5.33	NBR
O-Ring	28	31	1.5	NBR
O-Ring	28	32	2	NBR
O-Ring	28	33	2.5	NBR
O-Ring	28	34	3	NBR
O-Ring	28	35	3.5	NBR
O-Ring	28	36	4	NBR
O-Ring	28	38	5	NBR
O-Ring	28.24	33.48	2.62	NBR
O-Ring	28.3	31.86	1.78	NBR
O-Ring	29	32	1.5	NBR
O-Ring	29	33	2	NBR
O-Ring	29	34	2.5	NBR
O-Ring	29	35	3	NBR
O-Ring	29	36	3.5	NBR
O-Ring	29	37	4	NBR
O-Ring	29	39	5	NBR
O-Ring	29.4	34.4	2.5	NBR
O-Ring	29.5	35.5	3	NBR
O-Ring	29.51	40.17	5.33	NBR
O-Ring	29.74	35.62	2.94	NBR
O-Ring	29.74	36.8	3.53	NBR
O-Ring	29.87	33.43	1.78	NBR
O-Ring	30	33	1.5	NBR
O-Ring	30	34	2	NBR
O-Ring	30	35	2.5	NBR
O-Ring	30	36	3	NBR
O-Ring	30	37	3.5	NBR
O-Ring	30	38	4	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	30	40	5	NBR
O-Ring	30	42	6	NBR
O-Ring	30.5	38.5	4	NBR
O-Ring	31	34	1.5	NBR
O-Ring	31	35	2	NBR
O-Ring	31	36	2.5	NBR
O-Ring	31	37	3	NBR
O-Ring	31	38	3.5	NBR
O-Ring	31	39	4	NBR
O-Ring	31	41	5	NBR
O-Ring	31.12	41.78	5.33	NBR
O-Ring	31.34	38.4	3.53	NBR
O-Ring	31.42	36.66	2.62	NBR
O-Ring	31.47	35.03	1.78	NBR
O-Ring	31.5	36.5	2.5	NBR
O-Ring	31.5	37.5	3	NBR
O-Ring	31.7	38.7	3.5	NBR
O-Ring	32	35	1.5	NBR
O-Ring	32	36	2	NBR
O-Ring	32	37	2.5	NBR
O-Ring	32	39	3.5	NBR
O-Ring	32	40	4	NBR
O-Ring	32	42	5	NBR
O-Ring	32.5	38.5	3	NBR
O-Ring	32.5	39.5	3.5	NBR
O-Ring	32.69	43.35	5.33	NBR
O-Ring	32.92	39.98	3.53	NBR
O-Ring	32.99	38.23	2.62	NBR
O-Ring	33	36	1.5	NBR
O-Ring	33	37	2	NBR
O-Ring	33	38	2.5	NBR
O-Ring	33	39	3	NBR
O-Ring	33	40	3.5	NBR
O-Ring	33	41	4	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	33	43	5	NBR
O-Ring	33.05	36.61	1.78	NBR
O-Ring	33.3	38.1	2.4	NBR
O-Ring	33.3	38.1	2.4	NBR
O-Ring	34	37	1.5	NBR
O-Ring	34	38	2	NBR
O-Ring	34	39	2.5	NBR
O-Ring	34	40	3	NBR
O-Ring	34	41	3.5	NBR
O-Ring	34	42	4	NBR
O-Ring	34	44	5	NBR
O-Ring	34.29	44.95	5.33	NBR
O-Ring	34.5	40.5	3	NBR
O-Ring	34.5	42.5	4	NBR
O-Ring	34.52	41.58	3.53	NBR
O-Ring	34.59	39.83	2.62	NBR
O-Ring	34.65	38.21	1.78	NBR
O-Ring	35	37	1	NBR
O-Ring	35	38	1.5	NBR
O-Ring	35	39	2	NBR
O-Ring	35	40	2.5	NBR
O-Ring	35	41	3	NBR
O-Ring	35	42	3.5	NBR
O-Ring	35	43	4	NBR
O-Ring	35	45	5	NBR
O-Ring	35.5	41.5	3	NBR
O-Ring	35.76	41	2.62	NBR
O-Ring	36	39	1.5	NBR
O-Ring	36	40	2	NBR
O-Ring	36	41	2.5	NBR
O-Ring	36	42	3	NBR
O-Ring	36	44	4	NBR
O-Ring	36	46	5	NBR
O-Ring	36.09	43.15	3.53	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	36.17	41.41	2.62	NBR
O-Ring	36.27	39.83	1.78	NBR
O-Ring	36.5	41.5	2.5	NBR
O-Ring	36.5	42.5	3	NBR
O-Ring	37	40	1.5	NBR
O-Ring	37	41	2	NBR
O-Ring	37	42	2.5	NBR
O-Ring	37	43	3	NBR
O-Ring	37	44	3.5	NBR
O-Ring	37	45	4	NBR
O-Ring	37	47	5	NBR
O-Ring	37.1	40.3	1.6	NBR
O-Ring	37.4	44.4	3.5	NBR
O-Ring	37.47	48.13	5.33	NBR
O-Ring	37.5	42.5	2.5	NBR
O-Ring	37.5	43.5	3	NBR
O-Ring	37.69	44.75	3.53	NBR
O-Ring	37.69	44.75	3.53	NBR
O-Ring	37.77	43.01	2.62	NBR
O-Ring	37.82	41.38	1.78	NBR
O-Ring	38	41	1.5	NBR
O-Ring	38	42	2	NBR
O-Ring	38	43	2.5	NBR
O-Ring	38	44	3	NBR
O-Ring	38	45	3.5	NBR
O-Ring	38	46	4	NBR
O-Ring	38	47	4.5	NBR
O-Ring	38	48	5	NBR
O-Ring	38	49	5.5	NBR
O-Ring	38.7	44.7	3	NBR
O-Ring	39	42	1.5	NBR
O-Ring	39	43	2	NBR
O-Ring	39	44	2.5	NBR
O-Ring	39	45	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	39	46	3.5	NBR
O-Ring	39	47	4	NBR
O-Ring	39	50	5.5	NBR
O-Ring	39.34	44.58	2.62	NBR
O-Ring	39.45	43.01	1.78	NBR
O-Ring	39.5	43.5	2	NBR
O-Ring	39.5	45.5	3	NBR
O-Ring	39.7	46.76	3.53	NBR
O-Ring	40	42	1	NBR
O-Ring	40	43	1.5	NBR
O-Ring	40	44	2	NBR
O-Ring	40	45	2.5	NBR
O-Ring	40	46	3	NBR
O-Ring	40	48	4	NBR
O-Ring	40	50	5	NBR
O-Ring	40	50.6	5.3	NBR
O-Ring	40	51	5.5	NBR
O-Ring	40.2	46.2	3	NBR
O-Ring	40.5	43.5	1.5	NBR
O-Ring	40.64	51.3	5.33	NBR
O-Ring	40.87	47.93	3.53	NBR
O-Ring	40.94	46.18	2.62	NBR
O-Ring	41	44.56	1.78	NBR
O-Ring	41	45	2	NBR
O-Ring	41	46	2.5	NBR
O-Ring	41	47	3	NBR
O-Ring	41	49	4	NBR
O-Ring	41	50	4.5	NBR
O-Ring	41	52	5.5	NBR
O-Ring	41.28	48.34	3.53	NBR
O-Ring	41.5	47.5	3	NBR
O-Ring	42	45	1.5	NBR
O-Ring	42	46	2	NBR
O-Ring	42	47	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	42	48	3	NBR
O-Ring	42	48.4	3.2	NBR
O-Ring	42	49	3.5	NBR
O-Ring	42	50	4	NBR
O-Ring	42	51	4.5	NBR
O-Ring	42	52	5	NBR
O-Ring	42	54	6	NBR
O-Ring	42.5	48.5	3	NBR
O-Ring	42.52	47.76	2.62	NBR
O-Ring	42.86	49.92	3.53	NBR
O-Ring	43	47	2	NBR
O-Ring	43	48	2.5	NBR
O-Ring	43	49	3	NBR
O-Ring	43	51	4	NBR
O-Ring	43.82	54.48	5.33	NBR
O-Ring	44	48	2	NBR
O-Ring	44	48.8	2.4	NBR
O-Ring	44	49	2.5	NBR
O-Ring	44	52	4	NBR
O-Ring	44	54	5	NBR
O-Ring	44	55	5.5	NBR
O-Ring	44.04	51.1	3.53	NBR
O-Ring	44.12	49.36	2.62	NBR
O-Ring	44.17	47.73	1.78	NBR
O-Ring	44.3	55.7	5.7	NBR
O-Ring	44.5	48.1	1.8	NBR
O-Ring	44.5	50.5	3	NBR
O-Ring	44.6	49.4	2.4	NBR
O-Ring	45	48.6	1.8	NBR
O-Ring	45	49	2	NBR
O-Ring	45	50	2.5	NBR
O-Ring	45	51	3	NBR
O-Ring	45	52	3.5	NBR
O-Ring	45	53	4	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	45	54	4.5	NBR
O-Ring	45	55	5	NBR
O-Ring	45	56	5.5	NBR
O-Ring	45	59	7	NBR
O-Ring	45.5		5	NBR
O-Ring	45.69	50.93	2.62	NBR
O-Ring	46	49	1.5	NBR
O-Ring	46	49.6	1.8	NBR
O-Ring	46	50	2	NBR
O-Ring	46	51	2.5	NBR
O-Ring	46	52	3	NBR
O-Ring	46	53	3.5	NBR
O-Ring	46	54	4	NBR
O-Ring	46	56	5	NBR
O-Ring	46.78	52.02	2.62	NBR
O-Ring	46.99	57.65	5.33	NBR
O-Ring	47	50	1.5	NBR
O-Ring	47	51	2	NBR
O-Ring	47	52	2.5	NBR
O-Ring	47	53	3	NBR
O-Ring	47	55	4	NBR
O-Ring	47	57	5	NBR
O-Ring	47.22	54.28	3.53	NBR
O-Ring	47.22	54.28	3.53	NBR
O-Ring	47.29	52.53	2.62	NBR
O-Ring	47.35	50.91	1.78	NBR
O-Ring	48	52	2	NBR
O-Ring	48	53	2.5	NBR
O-Ring	48	54	3	NBR
O-Ring	48	55	3.5	NBR
O-Ring	48	56	4	NBR
O-Ring	48	58	5	NBR
O-Ring	48	60	6	NBR
O-Ring	48.9	54.14	2.62	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	49	52	1.5	NBR
O-Ring	49	53	2	NBR
O-Ring	49	54	2.5	NBR
O-Ring	49	55	3	NBR
O-Ring	49	56	3.5	NBR
O-Ring	49	57	4	NBR
O-Ring	49	59	5	NBR
O-Ring	49.2	60.6	5.7	NBR
O-Ring	49.5	55.5	3	NBR
O-Ring	50	53	1.5	NBR
O-Ring	50	54	2	NBR
O-Ring	50	55	2.5	NBR
O-Ring	50	56	3	NBR
O-Ring	50	57	3.5	NBR
O-Ring	50	58	4	NBR
O-Ring	50	59	4.5	NBR
O-Ring	50	60	5	NBR
O-Ring	50	61	5.5	NBR
O-Ring	50	62	6	NBR
O-Ring	50.17	60.83	5.33	NBR
O-Ring	50.39	57.45	3.53	NBR
O-Ring	50.47	55.71	2.62	NBR
O-Ring	50.52	54.08	1.78	NBR
O-Ring	51	55	2	NBR
O-Ring	51	56	2.5	NBR
O-Ring	51	57	3	NBR
O-Ring	51	58	3.5	NBR
O-Ring	51	59	4	NBR
O-Ring	51	61	5	NBR
O-Ring	51.5	55.5	2	NBR
O-Ring	51.5	58.5	3.5	NBR
O-Ring	51.6	56.4	2.4	NBR
O-Ring	52	55.6	1.8	NBR
O-Ring	52	56	2	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	52	57	2.5	NBR
O-Ring	52	58	3	NBR
O-Ring	52	60	4	NBR
O-Ring	52	62	5	NBR
O-Ring	52	64	6	NBR
O-Ring	52.07	57.31	2.62	NBR
O-Ring	52.3	63.7	5.7	NBR
O-Ring	53	57	2	NBR
O-Ring	53	58	2.5	NBR
O-Ring	53	59	3	NBR
O-Ring	53	60	3.5	NBR
O-Ring	53	61	4	NBR
O-Ring	53	63	5	NBR
O-Ring	53	64	5.5	NBR
O-Ring	53	65	6	NBR
O-Ring	53.34	64	5.33	NBR
O-Ring	53.57	60.63	3.53	NBR
O-Ring	53.64	58.88	2.62	NBR
O-Ring	53.7	57.26	1.78	NBR
O-Ring	54	57	1.5	NBR
O-Ring	54	58	2	NBR
O-Ring	54	59	2.5	NBR
O-Ring	54	60	3	NBR
O-Ring	54	60.6	3.3	NBR
O-Ring	54	61	3.5	NBR
O-Ring	54	62	4	NBR
O-Ring	54	64	5	NBR
O-Ring	54	65	5.5	NBR
O-Ring	54.43	58.43	2	NBR
O-Ring	54.5	60.5	3	NBR
O-Ring	54.6	66	5.7	NBR
O-Ring	55	58	1.5	NBR
O-Ring	55	59	2	NBR
O-Ring	55	60	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	55	61	3	NBR
O-Ring	55	62	3.5	NBR
O-Ring	55	63	4	NBR
O-Ring	55	65	5	NBR
O-Ring	55	66	5.5	NBR
O-Ring	55	67	6	NBR
O-Ring	55.25	60.49	2.62	NBR
O-Ring	55.5	61.5	3	NBR
O-Ring	56	59.5	1.75	NBR
O-Ring	56	60	2	NBR
O-Ring	56	61	2.5	NBR
O-Ring	56	62	3	NBR
O-Ring	56	63	3.5	NBR
O-Ring	56	64	4	NBR
O-Ring	56	65	4.5	NBR
O-Ring	56	66	5	NBR
O-Ring	56	68	6	NBR
O-Ring	56.52	67.18	5.33	NBR
O-Ring	56.74	63.8	3.53	NBR
O-Ring	56.74	63.8	3.53	NBR
O-Ring	56.82	62.06	2.62	NBR
O-Ring	56.87	60.43	1.78	NBR
O-Ring	57	62	2.5	NBR
O-Ring	57	63	3	NBR
O-Ring	57	64	3.5	NBR
O-Ring	57	65	4	NBR
O-Ring	57	67	5	NBR
O-Ring	57.5	63.7	3.1	NBR
O-Ring	58	62	2	NBR
O-Ring	58	63	2.5	NBR
O-Ring	58	64	3	NBR
O-Ring	58	65	3.5	NBR
O-Ring	58	66	4	NBR
O-Ring	58	68	5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	58	70	6	NBR
O-Ring	58.15	62.15	2	NBR
O-Ring	58.42	63.66	2.62	NBR
O-Ring	58.5	64.5	3	NBR
O-Ring	58.74	65.8	3.53	NBR
O-Ring	59	63	2	NBR
O-Ring	59	64	2.5	NBR
O-Ring	59	65	3	NBR
O-Ring	59	66	3.5	NBR
O-Ring	59	67	4	NBR
O-Ring	59.5	65.5	3	NBR
O-Ring	59.6	71	5.7	NBR
O-Ring	59.69	70.35	5.33	NBR
O-Ring	59.92	66.98	3.53	NBR
O-Ring	59.99	65.23	2.62	NBR
O-Ring	60	63	1.5	NBR
O-Ring	60	64	2	NBR
O-Ring	60	65	2.5	NBR
O-Ring	60	66	3	NBR
O-Ring	60	67	3.5	NBR
O-Ring	60	68	4	NBR
O-Ring	60	70	5	NBR
O-Ring	60	71	5.5	NBR
O-Ring	60	72	6	NBR
O-Ring	60.05	63.61	1.78	NBR
O-Ring	60.32	63.82	1.75	NBR
O-Ring	61	65	2	NBR
O-Ring	61	66	2.5	NBR
O-Ring	61	67	3	NBR
O-Ring	61	68	3.5	NBR
O-Ring	61	69	4	NBR
O-Ring	61	71	5	NBR
O-Ring	61.5	72.5	5.5	NBR
O-Ring	61.6	66.84	2.62	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	61.9	68.96	3.53	NBR
O-Ring	62	67	2.5	NBR
O-Ring	62	68	3	NBR
O-Ring	62	70	4	NBR
O-Ring	62	72	5	NBR
O-Ring	62	74	6	NBR
O-Ring	62.87	73.53	5.33	NBR
O-Ring	63	66	1.5	NBR
O-Ring	63	67	2	NBR
O-Ring	63	68	2.5	NBR
O-Ring	63	69	3	NBR
O-Ring	63	71	4	NBR
O-Ring	63	73	5	NBR
O-Ring	63	75	6	NBR
O-Ring	63.09	70.15	3.53	NBR
O-Ring	63.17	68.41	2.62	NBR
O-Ring	63.22	66.78	1.78	NBR
O-Ring	63.5	69.84	3.17	NBR
O-Ring	63.5	73.5	5	NBR
O-Ring	63.8	67.4	1.8	NBR
O-Ring	64	67	1.5	NBR
O-Ring	64	68	2	NBR
O-Ring	64	69	2.5	NBR
O-Ring	64	70	3	NBR
O-Ring	64	71	3.5	NBR
O-Ring	64	72	4	NBR
O-Ring	64	74	5	NBR
O-Ring	64.3	75.7	5.7	NBR
O-Ring	64.5	70.5	3	NBR
O-Ring	64.77	68.77	2	NBR
O-Ring	64.77	70.01	2.62	NBR
O-Ring	65	68	1.5	NBR
O-Ring	65	69	2	NBR
O-Ring	65	70	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	65	73	4	NBR
O-Ring	65	74	4.5	NBR
O-Ring	65	75	5	NBR
O-Ring	65	75.6	5.3	NBR
O-Ring	65	77	6	NBR
O-Ring	65.09	72.15	3.53	NBR
O-Ring	65.4	68.96	1.78	NBR
O-Ring	66	70	2	NBR
O-Ring	66	71	2.5	NBR
O-Ring	66	72	3	NBR
O-Ring	66	74	4	NBR
O-Ring	66.04	76.7	5.33	NBR
O-Ring	66.27	73.33	3.53	NBR
O-Ring	66.34	71.58	2.62	NBR
O-Ring	66.4	69.96	1.78	NBR
O-Ring	66.5	76.5	5	NBR
O-Ring	66.6	78	5.7	NBR
O-Ring	67	71	2	NBR
O-Ring	67	72	2.5	NBR
O-Ring	67	73	3	NBR
O-Ring	67	74	3.5	NBR
O-Ring	67	75	4	NBR
O-Ring	67	77	5	NBR
O-Ring	67	78	5.5	NBR
O-Ring	67.95	73.19	2.62	NBR
O-Ring	68	72	2	NBR
O-Ring	68	73	2.5	NBR
O-Ring	68	74	3	NBR
O-Ring	68	75	3.5	NBR
O-Ring	68	76	4	NBR
O-Ring	68	78	5	NBR
O-Ring	68	80	6	NBR
O-Ring	69	73	2	NBR
O-Ring	69	74	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	69	75	3	NBR
O-Ring	69	77	4	NBR
O-Ring	69	78	4.5	NBR
O-Ring	69	80	5.5	NBR
O-Ring	69.2	80.6	5.7	NBR
O-Ring	69.22	79.88	5.33	NBR
O-Ring	69.44	76.5	3.53	NBR
O-Ring	69.44	76.5	3.53	NBR
O-Ring	69.5	75.5	3	NBR
O-Ring	69.52	74.76	2.62	NBR
O-Ring	69.57	73.13	1.78	NBR
O-Ring	70	74	2	NBR
O-Ring	70	75	2.5	NBR
O-Ring	70	76	3	NBR
O-Ring	70	77	3.5	NBR
O-Ring	70	78	4	NBR
O-Ring	70	80	5	NBR
O-Ring	70	81	5.5	NBR
O-Ring	70	81.4	5.7	NBR
O-Ring	70	82	6	NBR
O-Ring	71	75	2	NBR
O-Ring	71	76	2.5	NBR
O-Ring	71	77	3	NBR
O-Ring	71	79	4	NBR
O-Ring	71	81	5	NBR
O-Ring	71.18	76.42	2.62	NBR
O-Ring	71.44	78.5	3.53	NBR
O-Ring	71.6	76.6	2.5	NBR
O-Ring	72	76	2	NBR
O-Ring	72	78	3	NBR
O-Ring	72	79	3.5	NBR
O-Ring	72	80	4	NBR
O-Ring	72	82	5	NBR
O-Ring	72.39	83.05	5.33	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	72.62	79.68	3.53	NBR
O-Ring	72.62	79.68	3.53	NBR
O-Ring	72.69	77.93	2.62	NBR
O-Ring	72.75	76.31	1.78	NBR
O-Ring	73	77	2	NBR
O-Ring	73	78	2.5	NBR
O-Ring	73	79	3	NBR
O-Ring	73	81	4	NBR
O-Ring	73	83	5	NBR
O-Ring	74	78	2	NBR
O-Ring	74	79	2.5	NBR
O-Ring	74	80	3	NBR
O-Ring	74	81	3.5	NBR
O-Ring	74	82	4	NBR
O-Ring	74	84	5	NBR
O-Ring	74.2	85.6	5.7	NBR
O-Ring	74.3	79.54	2.62	NBR
O-Ring	74.5	80.5	3	NBR
O-Ring	74.6	86	5.7	NBR
O-Ring	74.7	81.04	3.17	NBR
O-Ring	75	78	1.5	NBR
O-Ring	75	79	2	NBR
O-Ring	75	80	2.5	NBR
O-Ring	75	81	3	NBR
O-Ring	75	82	3.5	NBR
O-Ring	75	83	4	NBR
O-Ring	75	85	5	NBR
O-Ring	75	86	5.5	NBR
O-Ring	75	87	6	NBR
O-Ring	75.57	86.23	5.33	NBR
O-Ring	75.87	81.11	2.62	NBR
O-Ring	75.92	79.48	1.78	NBR
O-Ring	76	80	2	NBR
O-Ring	76	81	2.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	76	82	3	NBR
O-Ring	76	83	3.5	NBR
O-Ring	76	84	4	NBR
O-Ring	76	86	5	NBR
O-Ring	77	81	2	NBR
O-Ring	77	83	3	NBR
O-Ring	77	84	3.5	NBR
O-Ring	77	85	4	NBR
O-Ring	77.5	82.74	2.62	NBR
O-Ring	78	82	2	NBR
O-Ring	78	84	3	NBR
O-Ring	78	85	3.5	NBR
O-Ring	78	86	4	NBR
O-Ring	78	88	5	NBR
O-Ring	78	90	6	NBR
O-Ring	78.5	84.5	3	NBR
O-Ring	78.74	89.4	5.33	NBR
O-Ring	78.97	86.03	3.53	NBR
O-Ring	79	82.56	1.78	NBR
O-Ring	79	83	2	NBR
O-Ring	79	85	3	NBR
O-Ring	79	87	4	NBR
O-Ring	79	89	5	NBR
O-Ring	79.2	90.6	5.7	NBR
O-Ring	79.5	85.5	3	NBR
O-Ring	79.73	90.39	5.33	NBR
O-Ring	80	83	1.5	NBR
O-Ring	80	84	2	NBR
O-Ring	80	85	2.5	NBR
O-Ring	80	86	3	NBR
O-Ring	80	87	3.5	NBR
O-Ring	80	88	4	NBR
O-Ring	80	89	4.5	NBR
O-Ring	80	90	5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	80	91	5.5	NBR
O-Ring	80	92	6	NBR
O-Ring	80.6	85.84	2.62	NBR
O-Ring	81	84	1.5	NBR
O-Ring	81	85	2	NBR
O-Ring	81	87	3	NBR
O-Ring	81	91	5	NBR
O-Ring	81.92	92.58	5.33	NBR
O-Ring	82	86	2	NBR
O-Ring	82	87.2	2.5	NBR
O-Ring	82	88	3	NBR
O-Ring	82	90	4	NBR
O-Ring	82	92	5	NBR
O-Ring	82.14	89.2	3.53	NBR
O-Ring	82.22	87.46	2.62	NBR
O-Ring	82.27	85.83	1.78	NBR
O-Ring	83	87	2	NBR
O-Ring	83	88	2.5	NBR
O-Ring	83	89	3	NBR
O-Ring	83	90	3.5	NBR
O-Ring	83	95	6	NBR
O-Ring	83.8	89.04	2.62	NBR
O-Ring	84	88	2	NBR
O-Ring	84	90	3	NBR
O-Ring	84	91	3.5	NBR
O-Ring	84	92	4	NBR
O-Ring	84	94	5	NBR
O-Ring	84.5	90.5	3	NBR
O-Ring	85	89	2	NBR
O-Ring	85	90	2.5	NBR
O-Ring	85	91	3	NBR
O-Ring	85	93	4	NBR
O-Ring	85	95	5	NBR
O-Ring	85	95.4	5.2	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	85	96	5.5	NBR
O-Ring	85	97	6	NBR
O-Ring	85.09	95.75	5.33	NBR
O-Ring	85.32	92.38	3.53	NBR
O-Ring	85.34	88.9	1.78	NBR
O-Ring	86	90	2	NBR
O-Ring	86	92	3	NBR
O-Ring	86	93	3.5	NBR
O-Ring	86	94	4	NBR
O-Ring	87	90	1.5	NBR
O-Ring	87	91	2	NBR
O-Ring	87	93	3	NBR
O-Ring	87	95	4	NBR
O-Ring	87.5	97.5	5	NBR
O-Ring	88	91	1.5	NBR
O-Ring	88	92	2	NBR
O-Ring	88	93	2.5	NBR
O-Ring	88	94	3	NBR
O-Ring	88	96	4	NBR
O-Ring	88	98	5	NBR
O-Ring	88	100	6	NBR
O-Ring	88.27	95.33	3.53	NBR
O-Ring	88.27	98.93	5.33	NBR
O-Ring	88.49	95.55	3.53	NBR
O-Ring	88.57	93.81	2.62	NBR
O-Ring	88.62	92.18	1.78	NBR
O-Ring	89	95	3	NBR
O-Ring	89	99	5	NBR
O-Ring	89	100	5.5	NBR
O-Ring	89.2	100.6	5.7	NBR
O-Ring	89.69	100.35	5.33	NBR
O-Ring	90	94	2	NBR
O-Ring	90	95	2.5	NBR
O-Ring	90	96	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	90	97	3.5	NBR
O-Ring	90	98	4	NBR
O-Ring	90	100	5	NBR
O-Ring	90	101	5.5	NBR
O-Ring	90	102	6	NBR
O-Ring	90	104	7	NBR
O-Ring	91	96	2.5	NBR
O-Ring	91	99	4	NBR
O-Ring	91	101	5	NBR
O-Ring	91.44	102.1	5.33	NBR
O-Ring	91.7	95.26	1.78	NBR
O-Ring	92	96	2	NBR
O-Ring	92	97	2.5	NBR
O-Ring	92	98	3	NBR
O-Ring	92	100	4	NBR
O-Ring	92	102	5	NBR
O-Ring	92	104	6	NBR
O-Ring	93	97	2	NBR
O-Ring	93	99	3	NBR
O-Ring	93	100	3.5	NBR
O-Ring	93	101	4	NBR
O-Ring	93	105	6	NBR
O-Ring	94	98	2	NBR
O-Ring	94	99	2.5	NBR
O-Ring	94	100	3	NBR
O-Ring	94	101	3.5	NBR
O-Ring	94	102	4	NBR
O-Ring	94	106	6	NBR
O-Ring	94.5	100.5	3	NBR
O-Ring	94.6	106	5.7	NBR
O-Ring	94.62	105.28	5.33	NBR
O-Ring	94.84	101.9	3.53	NBR
O-Ring	94.92	100.16	2.62	NBR
O-Ring	94.97	98.53	1.78	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	95	99	2	NBR
O-Ring	95	100	2.5	NBR
O-Ring	95	101	3	NBR
O-Ring	95	102	3.5	NBR
O-Ring	95	103	4	NBR
O-Ring	95	104	4.5	NBR
O-Ring	95	105	5	NBR
O-Ring	95	107	6	NBR
O-Ring	96	100	2	NBR
O-Ring	96	101	2.5	NBR
O-Ring	96	102	3	NBR
O-Ring	96	103	3.5	NBR
O-Ring	96	106	5	NBR
O-Ring	97	101	2	NBR
O-Ring	97	102	2.5	NBR
O-Ring	97	103	3	NBR
O-Ring	97	105	4	NBR
O-Ring	97	107	5	NBR
O-Ring	97.79	108.45	5.33	NBR
O-Ring	98	102	2	NBR
O-Ring	98	103	2.5	NBR
O-Ring	98	104	3	NBR
O-Ring	98	106	4	NBR
O-Ring	98	108	5	NBR
O-Ring	98.05	101.61	1.78	NBR
O-Ring	98.5	105.5	3.5	NBR
O-Ring	99	105	3	NBR
O-Ring	99	106	3.5	NBR
O-Ring	99.3	110.7	5.7	NBR
O-Ring	99.5	105.5	3	NBR
O-Ring	100	103	1.5	NBR
O-Ring	100	104	2	NBR
O-Ring	100	105	2.5	NBR
O-Ring	100	106	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	100	106.4	3.2	NBR
O-Ring	100	108	4	NBR
O-Ring	100	110	5	NBR
O-Ring	100	110.66	5.33	NBR
O-Ring	100	111	5.5	NBR
O-Ring	100	112	6	NBR
O-Ring	100	120	10	NBR
O-Ring	100.97	111.63	5.33	NBR
O-Ring	101	107	3	NBR
O-Ring	101.19	108.25	3.53	NBR
O-Ring	101.27	106.51	2.62	NBR
O-Ring	102	106	2	NBR
O-Ring	102	107	2.5	NBR
O-Ring	102	108	3	NBR
O-Ring	102	109	3.5	NBR
O-Ring	102	110	4	NBR
O-Ring	102	112	5	NBR
O-Ring	103	107	2	NBR
O-Ring	103	109	3	NBR
O-Ring	103	115	6	NBR
O-Ring	104	107.56	1.78	NBR
O-Ring	104	109	2.5	NBR
O-Ring	104	110	3	NBR
O-Ring	104	112	4	NBR
O-Ring	104	114	5	NBR
O-Ring	104.14	114.8	5.33	NBR
O-Ring	104.3	115.7	5.7	NBR
O-Ring	104.37	111.43	3.53	NBR
O-Ring	104.4	110.8	3.2	NBR
O-Ring	105	109	2	NBR
O-Ring	105	110	2.5	NBR
O-Ring	105	111	3	NBR
O-Ring	105	113	4	NBR
O-Ring	105	115	5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	106	110	2	NBR
O-Ring	106	112	3	NBR
O-Ring	106	113	3.5	NBR
O-Ring	106	118	6	NBR
O-Ring	107	111	2	NBR
O-Ring	107	114	3.5	NBR
O-Ring	107	115	4	NBR
O-Ring	107	117	5	NBR
O-Ring	107.32	117.98	5.33	NBR
O-Ring	107.54	114.6	3.53	NBR
O-Ring	107.62	112.86	2.62	NBR
O-Ring	107.67	111.23	1.78	NBR
O-Ring	108	112	2	NBR
O-Ring	108	113	2.5	NBR
O-Ring	108	114	3	NBR
O-Ring	108	118	5	NBR
O-Ring	108	120	6	NBR
O-Ring	109	115	3	NBR
O-Ring	109	117	4	NBR
O-Ring	109.3	120.7	5.7	NBR
O-Ring	109.6	121	5.7	NBR
O-Ring	110	113	1.5	NBR
O-Ring	110	114	2	NBR
O-Ring	110	115	2.5	NBR
O-Ring	110	116	3	NBR
O-Ring	110	117	3.5	NBR
O-Ring	110	118	4	NBR
O-Ring	110	120	5	NBR
O-Ring	110	121	5.5	NBR
O-Ring	110	122	6	NBR
O-Ring	110.49	121.15	5.33	NBR
O-Ring	110.74	114.3	1.78	NBR
O-Ring	112	116	2	NBR
O-Ring	112	118	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	112	119	3.5	NBR
O-Ring	112	120	4	NBR
O-Ring	112	122	5	NBR
O-Ring	113	120	3.5	NBR
O-Ring	113	121	4	NBR
O-Ring	113	123	5	NBR
O-Ring	113	125	6	NBR
O-Ring	113.67	124.33	5.33	NBR
O-Ring	113.67	127.65	6.99	NBR
O-Ring	113.89	120.95	3.53	NBR
O-Ring	113.89	124.55	5.33	NBR
O-Ring	113.97	119.21	2.62	NBR
O-Ring	114	120	3	NBR
O-Ring	114	122	4	NBR
O-Ring	114.02	117.58	1.78	NBR
O-Ring	114.3	125.7	5.7	NBR
O-Ring	114.5	120.5	3	NBR
O-Ring	115	119	2	NBR
O-Ring	115	120	2.5	NBR
O-Ring	115	121	3	NBR
O-Ring	115	122	3.5	NBR
O-Ring	115	123	4	NBR
O-Ring	115	125	5	NBR
O-Ring	115	126	5.5	NBR
O-Ring	115	126.4	5.7	NBR
O-Ring	115	127	6	NBR
O-Ring	116	120	2	NBR
O-Ring	116	126	5	NBR
O-Ring	116.84	127.5	5.33	NBR
O-Ring	116.84	130.82	6.99	NBR
O-Ring	117	123	3	NBR
O-Ring	117	125	4	NBR
O-Ring	117.07	124.13	3.53	NBR
O-Ring	117.1	120.66	1.78	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	118	122	2	NBR
O-Ring	118	124	3	NBR
O-Ring	118	126	4	NBR
O-Ring	118	128	5	NBR
O-Ring	118	130	6	NBR
O-Ring	118.5	125.5	3.5	NBR
O-Ring	119	125	3	NBR
O-Ring	119.2	130.6	5.7	NBR
O-Ring	120	125	2.5	NBR
O-Ring	120	126	3	NBR
O-Ring	120	128	4	NBR
O-Ring	120	130	5	NBR
O-Ring	120	131	5.5	NBR
O-Ring	120	132	6	NBR
O-Ring	120.02	130.68	5.33	NBR
O-Ring	120.19	134.17	6.99	NBR
O-Ring	120.24	127.3	3.53	NBR
O-Ring	120.32	125.56	2.62	NBR
O-Ring	120.37	123.93	1.78	NBR
O-Ring	120.5	129.5	4.5	NBR
O-Ring	122	126	2	NBR
O-Ring	122	127	2.5	NBR
O-Ring	122	128	3	NBR
O-Ring	122	129	3.5	NBR
O-Ring	122	130	4	NBR
O-Ring	122	132.6	5.3	NBR
O-Ring	123	131	4	NBR
O-Ring	123	133	5	NBR
O-Ring	123.19	133.85	5.33	NBR
O-Ring	123.19	137.17	6.99	NBR
O-Ring	123.42	130.48	3.53	NBR
O-Ring	123.44	127	1.78	NBR
O-Ring	124	130.4	3.2	NBR
O-Ring	124	132	4	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	124.3	135.7	5.7	NBR
O-Ring	125	129	2	NBR
O-Ring	125	130	2.5	NBR
O-Ring	125	131	3	NBR
O-Ring	125	132	3.5	NBR
O-Ring	125	133	4	NBR
O-Ring	125	135	5	NBR
O-Ring	125	137	6	NBR
O-Ring	126.37	137.03	5.33	NBR
O-Ring	126.37	140.35	6.99	NBR
O-Ring	126.59	133.65	3.53	NBR
O-Ring	126.67	131.91	2.62	NBR
O-Ring	126.72	130.28	1.78	NBR
O-Ring	127	132	2.5	NBR
O-Ring	127	134	3.5	NBR
O-Ring	127	135	4	NBR
O-Ring	127	137	5	NBR
O-Ring	128	132	2	NBR
O-Ring	128	134	3	NBR
O-Ring	128	137	4.5	NBR
O-Ring	128	138	5	NBR
O-Ring	128	140	6	NBR
O-Ring	129	140	5.5	NBR
O-Ring	129.4	132.96	1.78	NBR
O-Ring	129.54	140.2	5.33	NBR
O-Ring	129.54	143.52	6.99	NBR
O-Ring	130	134	2	NBR
O-Ring	130	136	3	NBR
O-Ring	130	137	3.5	NBR
O-Ring	130	138	4	NBR
O-Ring	130	140	5	NBR
O-Ring	130	141	5.5	NBR
O-Ring	130	142	6	NBR
O-Ring	130	144	7	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	132	138	3	NBR
O-Ring	132	140	4	NBR
O-Ring	132	142	5	NBR
O-Ring	132	144	6	NBR
O-Ring	132.72	143.38	5.33	NBR
O-Ring	132.72	146.7	6.99	NBR
O-Ring	132.94	140	3.53	NBR
O-Ring	133	139	3	NBR
O-Ring	133.02	138.26	2.62	NBR
O-Ring	133.07	136.63	1.78	NBR
O-Ring	134	142	4	NBR
O-Ring	134.3	145.7	5.7	NBR
O-Ring	134.5	140.5	3	NBR
O-Ring	135	139	2	NBR
O-Ring	135	140	2.5	NBR
O-Ring	135	142.06	3.53	NBR
O-Ring	135	143	4	NBR
O-Ring	135	145	5	NBR
O-Ring	135	147	6	NBR
O-Ring	135.76	139.32	1.78	NBR
O-Ring	135.89	146.55	5.33	NBR
O-Ring	135.89	149.87	6.99	NBR
O-Ring	136	142	3	NBR
O-Ring	136	148	6	NBR
O-Ring	136.12	143.18	3.53	NBR
O-Ring	138	142	2	NBR
O-Ring	138	144	3	NBR
O-Ring	138	145	3.5	NBR
O-Ring	138	146	4	NBR
O-Ring	138	148	5	NBR
O-Ring	138	150	6	NBR
O-Ring	139.07	149.73	5.33	NBR
O-Ring	139.07	153.05	6.99	NBR
O-Ring	139.29	146.35	3.53	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	139.37	144.61	2.62	NBR
O-Ring	140	144	1	NBR
O-Ring	140	145	2.5	NBR
O-Ring	140	146	3	NBR
O-Ring	140	147	3.5	NBR
O-Ring	140	148	4	NBR
O-Ring	140	150	5	NBR
O-Ring	140	151	5.5	NBR
O-Ring	140	152	6	NBR
O-Ring	140	154	7	NBR
O-Ring	142	146	2	NBR
O-Ring	142	147	2.5	NBR
O-Ring	142	148	3	NBR
O-Ring	142	150	4	NBR
O-Ring	142	152	5	NBR
O-Ring	142.24	152.9	5.33	NBR
O-Ring	142.24	156.22	6.99	NBR
O-Ring	142.47	149.53	3.53	NBR
O-Ring	143	149	3	NBR
O-Ring	143	150	3.5	NBR
O-Ring	145	149	2	NBR
O-Ring	145	150	2.5	NBR
O-Ring	145	151	3	NBR
O-Ring	145	153	4	NBR
O-Ring	145	155	5	NBR
O-Ring	145	156	5.5	NBR
O-Ring	145.42	156.08	5.33	NBR
O-Ring	145.42	159.4	6.99	NBR
O-Ring	145.64	152.7	3.53	NBR
O-Ring	145.72	150.96	2.62	NBR
O-Ring	147	154	3.5	NBR
O-Ring	147	157	5	NBR
O-Ring	148	154	3	NBR
O-Ring	148	155	3.5	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	148	156	4	NBR
O-Ring	148	160	6	NBR
O-Ring	148.59	159.25	5.33	NBR
O-Ring	148.59	162.57	6.99	NBR
O-Ring	148.82	155.88	3.53	NBR
O-Ring	150	154	2	NBR
O-Ring	150	155	2.5	NBR
O-Ring	150	156	3	NBR
O-Ring	150	157	3.5	NBR
O-Ring	150	158	4	NBR
O-Ring	150	160	5	NBR
O-Ring	150	161	5.5	NBR
O-Ring	150	162	6	NBR
O-Ring	150	164	7	NBR
O-Ring	150	166	8	NBR
O-Ring	151	161	5	NBR
O-Ring	151.77	162.43	5.33	NBR
O-Ring	151.77	165.75	6.99	NBR
O-Ring	151.99	159.05	3.53	NBR
O-Ring	152	156	2	NBR
O-Ring	152	160	4	NBR
O-Ring	152.07	157.31	2.62	NBR
O-Ring	154	160	3	NBR
O-Ring	154	161	3.5	NBR
O-Ring	154	162	4	NBR
O-Ring	155	160	2.5	NBR
O-Ring	155	161	3	NBR
O-Ring	155	163	4	NBR
O-Ring	155	165	5	NBR
O-Ring	156	163	3.5	NBR
O-Ring	158	168	5	NBR
O-Ring	158.12	168.78	5.33	NBR
O-Ring	158.12	172.1	6.99	NBR
O-Ring	158.34	165.4	3.53	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	158.42	163.66	2.62	NBR
O-Ring	159.3	170.7	5.7	NBR
O-Ring	160	164	2	NBR
O-Ring	160	165	2.5	NBR
O-Ring	160	166	3	NBR
O-Ring	160	168	4	NBR
O-Ring	160	170	5	NBR
O-Ring	160	171	5.5	NBR
O-Ring	160	172	6	NBR
O-Ring	160	174	7	NBR
O-Ring	161	175	7	NBR
O-Ring	162	166	2	NBR
O-Ring	162	170	4	NBR
O-Ring	162	176	7	NBR
O-Ring	163	170	3.5	NBR
O-Ring	164	170	3	NBR
O-Ring	164	172	4	NBR
O-Ring	164	176	6	NBR
O-Ring	164.2	175.6	5.7	NBR
O-Ring	164.47	175.13	5.33	NBR
O-Ring	164.47	178.45	6.99	NBR
O-Ring	164.5	170.5	3	NBR
O-Ring	164.5	181.3	8.4	NBR
O-Ring	164.69	171.75	3.53	NBR
O-Ring	164.77	170.01	2.62	NBR
O-Ring	165	169	2	NBR
O-Ring	165	175	5	NBR
O-Ring	165	177	6	NBR
O-Ring	168	180	6	NBR
O-Ring	169	175	3	NBR
O-Ring	169.3	180.7	5.7	NBR
O-Ring	170	174	2	NBR
O-Ring	170	175	2.5	NBR
O-Ring	170	176	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	170	178	4	NBR
O-Ring	170	180	5	NBR
O-Ring	170	182	6	NBR
O-Ring	170.82	181.48	5.33	NBR
O-Ring	170.82	184.8	6.99	NBR
O-Ring	171.04	178.1	3.53	NBR
O-Ring	171.12	176.36	2.62	NBR
O-Ring	172	178	3	NBR
O-Ring	172	180	4	NBR
O-Ring	172	182	5	NBR
O-Ring	174	180	3	NBR
O-Ring	174	181	3.5	NBR
O-Ring	174.5	191.3	8.4	NBR
O-Ring	175	179	2	NBR
O-Ring	175	180	2.5	NBR
O-Ring	175	181	3	NBR
O-Ring	175	183	4	NBR
O-Ring	175	185	5	NBR
O-Ring	177.17	187.83	5.33	NBR
O-Ring	177.17	191.15	6.99	NBR
O-Ring	177.39	184.45	3.53	NBR
O-Ring	178	184	3	NBR
O-Ring	179	185	3	NBR
O-Ring	179.3	190.7	5.7	NBR
O-Ring	180	184	2	NBR
O-Ring	180	186	3	NBR
O-Ring	180	187	3.5	NBR
O-Ring	180	188	4	NBR
O-Ring	180	190	5	NBR
O-Ring	180	192	6	NBR
O-Ring	180	194	7	NBR
O-Ring	182	187	2.5	NBR
O-Ring	182	188	3	NBR
O-Ring	182	196	7	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	183	189	3	NBR
O-Ring	183.52	194.18	5.33	NBR
O-Ring	183.52	197.5	6.99	NBR
O-Ring	183.74	190.8	3.53	NBR
O-Ring	184	196	6	NBR
O-Ring	184.3	195.7	5.7	NBR
O-Ring	185	189	2	NBR
O-Ring	185	191	3	NBR
O-Ring	185	192	3.5	NBR
O-Ring	185	193	4	NBR
O-Ring	185	195	5	NBR
O-Ring	187	193	3	NBR
O-Ring	188	195	3.5	NBR
O-Ring	188	200	6	NBR
O-Ring	189.3	200.7	5.7	NBR
O-Ring	189.87	200.53	5.33	NBR
O-Ring	189.87	203.85	6.99	NBR
O-Ring	190	198	4	NBR
O-Ring	190	200	5	NBR
O-Ring	190	201	5.5	NBR
O-Ring	190	202	6	NBR
O-Ring	190	204	7	NBR
O-Ring	190.09	197.15	3.53	NBR
O-Ring	190.17	195.41	2.62	NBR
O-Ring	192	198	3	NBR
O-Ring	192	200	4	NBR
O-Ring	192	202	5	NBR
O-Ring	194	202	4	NBR
O-Ring	194.3	205.7	5.7	NBR
O-Ring	195	201	3	NBR
O-Ring	196.22	206.88	5.33	NBR
O-Ring	196.22	210.2	6.99	NBR
O-Ring	196.44	203.5	3.53	NBR
O-Ring	196.52	201.76	2.62	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	199.2	210.6	5.7	NBR
O-Ring	200	205	2.5	NBR
O-Ring	200	206	3	NBR
O-Ring	200	207	3.5	NBR
O-Ring	200	208	4	NBR
O-Ring	200	210	5	NBR
O-Ring	200	212	6	NBR
O-Ring	202.57	213.23	5.33	NBR
O-Ring	202.57	216.55	6.99	NBR
O-Ring	202.79	209.85	3.53	NBR
O-Ring	202.87	208.11	2.62	NBR
O-Ring	205	211	3	NBR
O-Ring	205	215	5	NBR
O-Ring	205	217	6	NBR
O-Ring	208.92	219.58	5.33	NBR
O-Ring	209.14	216.2	3.53	NBR
O-Ring	209.22	214.46	2.62	NBR
O-Ring	209.3	220.7	5.7	NBR
O-Ring	210	216	3	NBR
O-Ring	210	218	4	NBR
O-Ring	210	220	5	NBR
O-Ring	210	222	6	NBR
O-Ring	212	218	3	NBR
O-Ring	215	221	3	NBR
O-Ring	215	225	5	NBR
O-Ring	215.27	225.93	5.33	NBR
O-Ring	215.27	229.25	6.99	NBR
O-Ring	215.49	222.55	3.53	NBR
O-Ring	218	226	4	NBR
O-Ring	218	228.6	5.3	NBR
O-Ring	218	230	6	NBR
O-Ring	219.3	230.7	5.7	NBR
O-Ring	220	226	3	NBR
O-Ring	220	228	4	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	220	230	5	NBR
O-Ring	220	232	6	NBR
O-Ring	220	236	8	NBR
O-Ring	221.62	232.28	5.33	NBR
O-Ring	221.84	228.9	3.53	NBR
O-Ring	225	231	3	NBR
O-Ring	225	233	4	NBR
O-Ring	225	235	5	NBR
O-Ring	227.97	238.63	5.33	NBR
O-Ring	227.97	241.95	6.99	NBR
O-Ring	228.19	235.25	3.53	NBR
O-Ring	229.3	240.7	5.7	NBR
O-Ring	230	235	2.5	NBR
O-Ring	230	236	3	NBR
O-Ring	230	238	4	NBR
O-Ring	230	240	5	NBR
O-Ring	234	244	5	NBR
O-Ring	234.32	244.98	5.33	NBR
O-Ring	234.54	241.6	3.53	NBR
O-Ring	236	250	7	NBR
O-Ring	239.3	250.7	5.7	NBR
O-Ring	240	246	3	NBR
O-Ring	240	248	4	NBR
O-Ring	240	250	5	NBR
O-Ring	240	252	6	NBR
O-Ring	240.67	251.33	5.33	NBR
O-Ring	240.67	254.65	6.99	NBR
O-Ring	240.89	247.95	3.53	NBR
O-Ring	245	251	3	NBR
O-Ring	247	259	6	NBR
O-Ring	247.02	257.68	5.33	NBR
O-Ring	247.24	254.3	3.53	NBR
O-Ring	249.3	260.7	5.7	NBR
O-Ring	250	256	3	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	250	257	3.5	NBR
O-Ring	250	258	4	NBR
O-Ring	250	260	5	NBR
O-Ring	250	262	6	NBR
O-Ring	250	264	7	NBR
O-Ring	253.37	267.35	6.99	NBR
O-Ring	253.59	260.65	3.53	NBR
O-Ring	259.3	270.7	5.7	NBR
O-Ring	260	266	3	NBR
O-Ring	260	268	4	NBR
O-Ring	260	270	5	NBR
O-Ring	265	275	5	NBR
O-Ring	265	279	7	NBR
O-Ring	266.07	276.73	5.33	NBR
O-Ring	266.07	280.05	6.99	NBR
O-Ring	266.29	273.35	3.53	NBR
O-Ring	269.3	280.7	5.7	NBR
O-Ring	270	276	3	NBR
O-Ring	270	280	5	NBR
O-Ring	270	282	6	NBR
O-Ring	275	285	5	NBR
O-Ring	278.77	289.43	5.33	NBR
O-Ring	278.77	292.75	6.99	NBR
O-Ring	278.99	286.05	3.53	NBR
O-Ring	279.3	290.7	5.7	NBR
O-Ring	280	286	3	NBR
O-Ring	280	290	5	NBR
O-Ring	280	292	6	NBR
O-Ring	280	294	7	NBR
O-Ring	285	291	3	NBR
O-Ring	285	299	7	NBR
O-Ring	289.3	300.7	5.7	NBR
O-Ring	290	300	5	NBR
O-Ring	291.47	302.13	5.33	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	291.5	305.5	7	NBR
O-Ring	291.69	298.75	3.53	NBR
O-Ring	295	307	6	NBR
O-Ring	299.3	310.7	5.7	NBR
O-Ring	300	306	3	NBR
O-Ring	300	310	5	NBR
O-Ring	300	312	6	NBR
O-Ring	300	316	8	NBR
O-Ring	304.17	314.83	5.33	NBR
O-Ring	304.17	318.17	7	NBR
O-Ring	304.39	311.45	3.53	NBR
O-Ring	305	315	5	NBR
O-Ring	305	319	7	NBR
O-Ring	310	320	5	NBR
O-Ring	310	322	6	NBR
O-Ring	315	325	5	NBR
O-Ring	315	327	6	NBR
O-Ring	316.87	330.85	6.99	NBR
O-Ring	319.3	330.7	5.7	NBR
O-Ring	320	334	7	NBR
O-Ring	329.57	340.23	5.33	NBR
O-Ring	329.57	343.55	6.99	NBR
O-Ring	329.79	336.85	3.53	NBR
O-Ring	330	338	4	NBR
O-Ring	330	340	5	NBR
O-Ring	334.5	351.3	8.4	NBR
O-Ring	335	345	5	NBR
O-Ring	339.5	356.3	8.4	NBR
O-Ring	340	350	5	NBR
O-Ring	340	354	7	NBR
O-Ring	350	360	5	NBR
O-Ring	354.5	371.3	8.4	NBR
O-Ring	354.97	365.63	5.33	NBR
O-Ring	355.19	362.25	3.53	NBR

O-RING



Profile	ID	OD	THK	Material
O-Ring	359.3	370.7	5.7	NBR
O-Ring	359.5	376.3	8.4	NBR
O-Ring	365	375	5	NBR
O-Ring	370	380	5	NBR
O-Ring	379.3	390.7	5.7	NBR
O-Ring	380.59	387.65	3.53	NBR
O-Ring	405.26	412.32	3.53	NBR
O-Ring	405.26	415.92	5.33	NBR
O-Ring	405.26	419.24	6.99	NBR
O-Ring	419.3	430.7	5.7	NBR
O-Ring	420	430	5	NBR
O-Ring	430	440	5	NBR
O-Ring	430	444	7	NBR
O-Ring	440	450	5	NBR
O-Ring	456	469.98	6.99	NBR
O-Ring	490	500	5	NBR
O-Ring	500	514	7	NBR
OR60031000-08	310	322	6	NBR
OR50031500-08	315	325	5	NBR
OR60031500-08	315	327	6	NBR
OR69931687-08	316.87	330.85	6.99	NBR
OR57031930-08	319.3	330.7	5.7	NBR
OR70032000-08	320	334	7	NBR
OR53332957-08	329.57	340.23	5.33	NBR
OR69932957-08	329.57	343.55	6.99	NBR
OR35332979-08	329.79	336.85	3.53	NBR
OR40033000-08	330	338	4	NBR
OR50033000-08	330	340	5	NBR
OR84033450-08	334.5	351.3	8.4	NBR
OR50033500-08	335	345	5	NBR
OR84033950-08	339.5	356.3	8.4	NBR
OR50034000-08	340	350	5	NBR
OR70034000-08	340	354	7	NBR
OR50035000-08	350	360	5	NBR

O-RING



Profile	ID	OD	THK	Material
OR84035450-08	354.5	371.3	8.4	NBR
OR53335497-08	354.97	365.63	5.33	NBR
OR35335519-08	355.19	362.25	3.53	NBR
OR57035930-08	359.3	370.7	5.7	NBR
OR84035950-08	359.5	376.3	8.4	NBR
OR50036500-08	365	375	5	NBR
OR50037000-08	370	380	5	NBR
OR57037930-08	379.3	390.7	5.7	NBR
OR35338059-08	380.59	387.65	3.53	NBR
OR35340526-08	405.26	412.32	3.53	NBR
OR53340526-08	405.26	415.92	5.33	NBR
OR69940526-08	405.26	419.24	6.99	NBR
OR57041930-08	419.3	430.7	5.7	NBR
OR50042000-08	420	430	5	NBR
OR50043000-08	430	440	5	NBR
OR70043000-08	430	444	7	NBR
OR50044000-08	440	450	5	NBR
OR69945600-08	456	469.98	6.99	NBR
OR50049000-08	490	500	5	NBR
OR70050000-08	500	514	7	NBR
O-Ring	2	4	1	FKM
O-Ring	2	5	1.5	FKM
O-Ring	2.57	6.13	1.78	FKM
O-Ring	2.9	6.46	1.78	FKM
O-Ring	3	5	1	FKM
O-Ring	3	6	1.5	FKM
O-Ring	3	7	2	FKM
O-Ring	3.2	6.4	1.6	FKM
O-Ring	3.5	6.5	1.5	FKM
O-Ring	3.68	7.24	1.78	FKM
O-Ring	4	6	1	FKM
O-Ring	4	7	1.5	FKM
O-Ring	4	7.6	1.8	FKM
O-Ring	4	8	2	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	4	9	2.5	FKM
O-Ring	4.3	7.3	1.5	FKM
O-Ring	4.34	11.4	3.53	FKM
O-Ring	4.47	8.03	1.78	FKM
O-Ring	4.5	7.5	1.5	FKM
O-Ring	5	7	1	FKM
O-Ring	5	7.6	1.3	FKM
O-Ring	5	8	1.5	FKM
O-Ring	5	8.56	1.78	FKM
O-Ring	5	9	2	FKM
O-Ring	5	10	2.5	FKM
O-Ring	5.28	8.84	1.78	FKM
O-Ring	5.5	8.5	1.5	FKM
O-Ring	5.94	13	3.53	FKM
O-Ring	6	8	1	FKM
O-Ring	6	9	1.5	FKM
O-Ring	6	10	2	FKM
O-Ring	6	11	2.5	FKM
O-Ring	6	12	3	FKM
O-Ring	6.02	11.26	2.62	FKM
O-Ring	6.07	9.63	1.78	FKM
O-Ring	6.5	9	1.5	FKM
O-Ring	6.5	10.1	1.8	FKM
O-Ring	6.5	10.5	2	FKM
O-Ring	6.75	10.31	1.78	FKM
O-Ring	7	9	1	FKM
O-Ring	7	10	1.5	FKM
O-Ring	7	11	2	FKM
O-Ring	7	12	2.5	FKM
O-Ring	7.4	11	1.8	FKM
O-Ring	7.5	10.5	1.5	FKM
O-Ring	7.5	11.5	2	FKM
O-Ring	7.5	12.5	2.5	FKM
O-Ring	7.52	14.58	3.53	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	7.59	12.83	2.62	FKM
O-Ring	7.65	11.21	1.78	FKM
O-Ring	8	10	1	FKM
O-Ring	8	11	1.5	FKM
O-Ring	8	11.6	1.8	FKM
O-Ring	8	12	2	FKM
O-Ring	8	12	2	FKM
O-Ring	8	14	3	FKM
O-Ring	8.3	13.1	2.4	FKM
O-Ring	8.4	11.4	1.5	FKM
O-Ring	8.4	12	1.8	FKM
O-Ring	8.5	12.5	2	FKM
O-Ring	8.73	12.29	1.78	FKM
O-Ring	9	11	1	FKM
O-Ring	9	12	1.5	FKM
O-Ring	9	12.6	1.8	FKM
O-Ring	9	13	2	FKM
O-Ring	9	14	2.5	FKM
O-Ring	9	15	3	FKM
O-Ring	9.12	16.18	3.53	FKM
O-Ring	9.19	14.43	2.62	FKM
O-Ring	9.25	12.81	1.78	FKM
O-Ring	9.5	12.5	1.5	FKM
O-Ring	9.5	13.1	1.8	FKM
O-Ring	9.5	13.5	2	FKM
O-Ring	9.5	14.5	2.5	FKM
O-Ring	9.8	12.8	1.5	FKM
O-Ring	9.8	13.6	1.9	FKM
O-Ring	10	13	1.5	FKM
O-Ring	10	13.6	1.8	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14.4	2.2	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	10	15	2.5	FKM
O-Ring	10	16	3	FKM
O-Ring	10.46	21.12	5.33	FKM
O-Ring	10.5	14.5	2	FKM
O-Ring	10.5	15.5	2.5	FKM
O-Ring	10.6	14.2	1.8	FKM
O-Ring	10.69	17.75	3.53	FKM
O-Ring	10.77	16.01	2.62	FKM
O-Ring	10.82	14.38	1.78	FKM
O-Ring	11	13	1	FKM
O-Ring	11	14	1.5	FKM
O-Ring	11	15	2	FKM
O-Ring	11	16	2.5	FKM
O-Ring	11	17	3	FKM
O-Ring	11.11	14.67	1.78	FKM
O-Ring	11.3	16.1	2.4	FKM
O-Ring	11.5	14.5	1.5	FKM
O-Ring	11.5	15.5	2	FKM
O-Ring	11.5	16.5	2.5	FKM
O-Ring	12	15	1.5	FKM
O-Ring	12	15.6	1.8	FKM
O-Ring	12	16	2	FKM
O-Ring	12	16	2	FKM
O-Ring	12	16	2	FKM
O-Ring	12	17	2.5	FKM
O-Ring	12	18	3	FKM
O-Ring	12.07	22.73	5.33	FKM
O-Ring	12.1	15.3	1.6	FKM
O-Ring	12.29	19.35	3.53	FKM
O-Ring	12.37	17.61	2.62	FKM
O-Ring	12.42	15.98	1.78	FKM
O-Ring	12.5	15	1.5	FKM
O-Ring	12.5	16.5	2	FKM
O-Ring	12.5	17.5	2.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	13	16	1.5	FKM
O-Ring	13	17	2	FKM
O-Ring	13	18	2.5	FKM
O-Ring	13	19	3	FKM
O-Ring	13.5	17.5	2	FKM
O-Ring	13.64	24.3	5.33	FKM
O-Ring	13.87	20.93	3.53	FKM
O-Ring	13.94	19.18	2.62	FKM
O-Ring	14	17	1.5	FKM
O-Ring	14	17.56	1.78	FKM
O-Ring	14	17.56	1.78	FKM
O-Ring	14	18	2	FKM
O-Ring	14	20	3	FKM
O-Ring	14	20	3	FKM
O-Ring	14.5	18.5	2	FKM
O-Ring	14.5	19.5	2.5	FKM
O-Ring	15	18	1.5	FKM
O-Ring	15	19	2	FKM
O-Ring	15	20	2.5	FKM
O-Ring	15	21	3	FKM
O-Ring	15	25	5	FKM
O-Ring	15.08	20.32	2.62	FKM
O-Ring	15.24	25.9	5.33	FKM
O-Ring	15.47	22.53	3.53	FKM
O-Ring	15.5	20.5	2.5	FKM
O-Ring	15.54	20.78	2.62	FKM
O-Ring	15.6	19.16	1.78	FKM
O-Ring	16	19	1.5	FKM
O-Ring	16	20	2	FKM
O-Ring	16	21	2.5	FKM
O-Ring	16	22	3	FKM
O-Ring	16	24	4	FKM
O-Ring	16.3	21.1	2.4	FKM
O-Ring	16.81	27.47	5.33	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	17	20	1.5	FKM
O-Ring	17	21	2	FKM
O-Ring	17	22	2.5	FKM
O-Ring	17	23	3	FKM
O-Ring	17.04	24.1	3.53	FKM
O-Ring	17.12	22.36	2.62	FKM
O-Ring	17.17	20.73	1.78	FKM
O-Ring	17.3	22.1	2.4	FKM
O-Ring	17.5	21.5	2	FKM
O-Ring	18	21	1.5	FKM
O-Ring	18	22	2	FKM
O-Ring	18	23	2.5	FKM
O-Ring	18	24	3	FKM
O-Ring	18	25	3.5	FKM
O-Ring	18	28	5	FKM
O-Ring	18.42	29.08	5.33	FKM
O-Ring	18.64	25.7	3.53	FKM
O-Ring	18.64	25.7	3.53	FKM
O-Ring	18.72	23.96	2.62	FKM
O-Ring	18.77	22.33	1.78	FKM
O-Ring	19	22	1.5	FKM
O-Ring	19	23	2	FKM
O-Ring	19	24	2.5	FKM
O-Ring	19	25	3	FKM
O-Ring	19	26	3.5	FKM
O-Ring	19.5	23.5	2	FKM
O-Ring	19.5	24.5	2.5	FKM
O-Ring	19.99	30.65	5.33	FKM
O-Ring	20	23	1.5	FKM
O-Ring	20	23.6	1.8	FKM
O-Ring	20	24	2	FKM
O-Ring	20	25	2.5	FKM
O-Ring	20	26	3	FKM
O-Ring	20	27	3.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	20	30	5	FKM
O-Ring	2	4	1	FKM
O-Ring	2	5	1.5	FKM
O-Ring	2.57	6.13	1.78	FKM
O-Ring	2.9	6.46	1.78	FKM
O-Ring	3	5	1	FKM
O-Ring	3	6	1.5	FKM
O-Ring	3	7	2	FKM
O-Ring	3.2	6.4	1.6	FKM
O-Ring	3.5	6.5	1.5	FKM
O-Ring	3.68	7.24	1.78	FKM
O-Ring	4	6	1	FKM
O-Ring	4	7	1.5	FKM
O-Ring	4	7.6	1.8	FKM
O-Ring	4	8	2	FKM
O-Ring	4	9	2.5	FKM
O-Ring	4.3	7.3	1.5	FKM
O-Ring	4.34	11.4	3.53	FKM
O-Ring	4.47	8.03	1.78	FKM
O-Ring	4.5	7.5	1.5	FKM
O-Ring	5	7	1	FKM
O-Ring	5	7.6	1.3	FKM
O-Ring	5	8	1.5	FKM
O-Ring	5	8.56	1.78	FKM
O-Ring	5	9	2	FKM
O-Ring	5	10	2.5	FKM
O-Ring	5.28	8.84	1.78	FKM
O-Ring	5.5	8.5	1.5	FKM
O-Ring	5.94	13	3.53	FKM
O-Ring	6	8	1	FKM
O-Ring	6	9	1.5	FKM
O-Ring	6	10	2	FKM
O-Ring	6	11	2.5	FKM
O-Ring	6	12	3	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	6.02	11.26	2.62	FKM
O-Ring	6.07	9.63	1.78	FKM
O-Ring	6.5	9	1.5	FKM
O-Ring	6.5	10.1	1.8	FKM
O-Ring	6.5	10.5	2	FKM
O-Ring	6.75	10.31	1.78	FKM
O-Ring	7	9	1	FKM
O-Ring	7	10	1.5	FKM
O-Ring	7	11	2	FKM
O-Ring	7	12	2.5	FKM
O-Ring	7.4	11	1.8	FKM
O-Ring	7.5	10.5	1.5	FKM
O-Ring	7.5	11.5	2	FKM
O-Ring	7.5	12.5	2.5	FKM
O-Ring	7.52	14.58	3.53	FKM
O-Ring	7.59	12.83	2.62	FKM
O-Ring	7.65	11.21	1.78	FKM
O-Ring	8	10	1	FKM
O-Ring	8	11	1.5	FKM
O-Ring	8	11.6	1.8	FKM
O-Ring	8	12	2	FKM
O-Ring	8	12	2	FKM
O-Ring	8	14	3	FKM
O-Ring	8.3	13.1	2.4	FKM
O-Ring	8.4	11.4	1.5	FKM
O-Ring	8.4	12	1.8	FKM
O-Ring	8.5	12.5	2	FKM
O-Ring	8.73	12.29	1.78	FKM
O-Ring	9	11	1	FKM
O-Ring	9	12	1.5	FKM
O-Ring	9	12.6	1.8	FKM
O-Ring	9	13	2	FKM
O-Ring	9	14	2.5	FKM
O-Ring	9	15	3	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	9.12	16.18	3.53	FKM
O-Ring	9.19	14.43	2.62	FKM
O-Ring	9.25	12.81	1.78	FKM
O-Ring	9.5	12.5	1.5	FKM
O-Ring	9.5	13.1	1.8	FKM
O-Ring	9.5	13.5	2	FKM
O-Ring	9.5	14.5	2.5	FKM
O-Ring	9.8	12.8	1.5	FKM
O-Ring	9.8	13.6	1.9	FKM
O-Ring	10	13	1.5	FKM
O-Ring	10	13.6	1.8	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14	2	FKM
O-Ring	10	14.4	2.2	FKM
O-Ring	10	15	2.5	FKM
O-Ring	10	16	3	FKM
O-Ring	10.46	21.12	5.33	FKM
O-Ring	10.5	14.5	2	FKM
O-Ring	10.5	15.5	2.5	FKM
O-Ring	10.6	14.2	1.8	FKM
O-Ring	10.69	17.75	3.53	FKM
O-Ring	10.77	16.01	2.62	FKM
O-Ring	10.82	14.38	1.78	FKM
O-Ring	11	13	1	FKM
O-Ring	11	14	1.5	FKM
O-Ring	11	15	2	FKM
O-Ring	11	16	2.5	FKM
O-Ring	11	17	3	FKM
O-Ring	11.11	14.67	1.78	FKM
O-Ring	11.3	16.1	2.4	FKM
O-Ring	11.5	14.5	1.5	FKM
O-Ring	11.5	15.5	2	FKM
O-Ring	11.5	16.5	2.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	12	15	1.5	FKM
O-Ring	12	15.6	1.8	FKM
O-Ring	12	16	2	FKM
O-Ring	12	16	2	FKM
O-Ring	12	16	2	FKM
O-Ring	12	17	2.5	FKM
O-Ring	12	18	3	FKM
O-Ring	12.07	22.73	5.33	FKM
O-Ring	12.1	15.3	1.6	FKM
O-Ring	12.29	19.35	3.53	FKM
O-Ring	12.37	17.61	2.62	FKM
O-Ring	12.42	15.98	1.78	FKM
O-Ring	12.5	15	1.5	FKM
O-Ring	12.5	16.5	2	FKM
O-Ring	12.5	17.5	2.5	FKM
O-Ring	13	16	1.5	FKM
O-Ring	13	17	2	FKM
O-Ring	13	18	2.5	FKM
O-Ring	13	19	3	FKM
O-Ring	13.5	17.5	2	FKM
O-Ring	13.64	24.3	5.33	FKM
O-Ring	13.87	20.93	3.53	FKM
O-Ring	13.94	19.18	2.62	FKM
O-Ring	14	17	1.5	FKM
O-Ring	14	17.56	1.78	FKM
O-Ring	14	17.56	1.78	FKM
O-Ring	14	18	2	FKM
O-Ring	14	20	3	FKM
O-Ring	14	20	3	FKM
O-Ring	14.5	18.5	2	FKM
O-Ring	14.5	19.5	2.5	FKM
O-Ring	15	18	1.5	FKM
O-Ring	15	19	2	FKM
O-Ring	15	20	2.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	15	21	3	FKM
O-Ring	15	25	5	FKM
O-Ring	15.08	20.32	2.62	FKM
O-Ring	15.24	25.9	5.33	FKM
O-Ring	15.47	22.53	3.53	FKM
O-Ring	15.5	20.5	2.5	FKM
O-Ring	15.54	20.78	2.62	FKM
O-Ring	15.6	19.16	1.78	FKM
O-Ring	16	19	1.5	FKM
O-Ring	16	20	2	FKM
O-Ring	16	21	2.5	FKM
O-Ring	16	22	3	FKM
O-Ring	16	24	4	FKM
O-Ring	16.3	21.1	2.4	FKM
O-Ring	16.81	27.47	5.33	FKM
O-Ring	17	20	1.5	FKM
O-Ring	17	21	2	FKM
O-Ring	17	22	2.5	FKM
O-Ring	17	23	3	FKM
O-Ring	17.04	24.1	3.53	FKM
O-Ring	17.12	22.36	2.62	FKM
O-Ring	17.17	20.73	1.78	FKM
O-Ring	17.3	22.1	2.4	FKM
O-Ring	17.5	21.5	2	FKM
O-Ring	18	21	1.5	FKM
O-Ring	18	22	2	FKM
O-Ring	18	23	2.5	FKM
O-Ring	18	24	3	FKM
O-Ring	18	25	3.5	FKM
O-Ring	18	28	5	FKM
O-Ring	18.42	29.08	5.33	FKM
O-Ring	18.64	25.7	3.53	FKM
O-Ring	18.64	25.7	3.53	FKM
O-Ring	18.72	23.96	2.62	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	18.77	22.33	1.78	FKM
O-Ring	19	22	1.5	FKM
O-Ring	19	23	2	FKM
O-Ring	19	24	2.5	FKM
O-Ring	19	25	3	FKM
O-Ring	19	26	3.5	FKM
O-Ring	19.5	23.5	2	FKM
O-Ring	19.5	24.5	2.5	FKM
O-Ring	19.99	30.65	5.33	FKM
O-Ring	20	23	1.5	FKM
O-Ring	20	23.6	1.8	FKM
O-Ring	20	24	2	FKM
O-Ring	20	25	2.5	FKM
O-Ring	20	26	3	FKM
O-Ring	20	27	3.5	FKM
O-Ring	20	30	5	FKM
O-Ring	20.22	27.28	3.53	FKM
O-Ring	20.29	25.53	2.62	FKM
O-Ring	20.3	25.1	2.4	FKM
O-Ring	20.35	23.91	1.78	FKM
O-Ring	21	24	1.5	FKM
O-Ring	21	25	2	FKM
O-Ring	21	26	2.5	FKM
O-Ring	21	27	3	FKM
O-Ring	21.3	26.1	2.4	FKM
O-Ring	21.59	32.25	5.33	FKM
O-Ring	21.82	28.88	3.53	FKM
O-Ring	21.89	27.13	2.62	FKM
O-Ring	21.95	25.51	1.78	FKM
O-Ring	22	25	1.5	FKM
O-Ring	22	26	2	FKM
O-Ring	22	27	2.5	FKM
O-Ring	22	28	3	FKM
O-Ring	22	30	4	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	22	32	5	FKM
O-Ring	22.5	26.5	2	FKM
O-Ring	23	26	1.5	FKM
O-Ring	23	27	2	FKM
O-Ring	23	28	2.5	FKM
O-Ring	23	29	3	FKM
O-Ring	23	30	3.5	FKM
O-Ring	23.16	33.82	5.33	FKM
O-Ring	23.39	30.45	3.53	FKM
O-Ring	23.47	28.71	2.62	FKM
O-Ring	23.52	27.08	1.78	FKM
O-Ring	24	27	1.5	FKM
O-Ring	24	28	2	FKM
O-Ring	24	29	2.5	FKM
O-Ring	24	30	3	FKM
O-Ring	24	31	3.5	FKM
O-Ring	24.4	30.6	3.1	FKM
O-Ring	24.5	32.5	4	FKM
O-Ring	24.77	35.43	5.33	FKM
O-Ring	24.99	32.05	3.53	FKM
O-Ring	24.99	32.05	3.53	FKM
O-Ring	25	28	1.5	FKM
O-Ring	25	29	2	FKM
O-Ring	25	30	2.5	FKM
O-Ring	25	31	3	FKM
O-Ring	25	33	4	FKM
O-Ring	25	35	5	FKM
O-Ring	25.07	30.31	2.62	FKM
O-Ring	25.12	28.68	1.78	FKM
O-Ring	25.3	30.1	2.4	FKM
O-Ring	25.5	29.5	2	FKM
O-Ring	26	29	1.5	FKM
O-Ring	26	30	2	FKM
O-Ring	26	31	2.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	26	32	3	FKM
O-Ring	26	33	3.5	FKM
O-Ring	26.34	37	5.33	FKM
O-Ring	26.5	30.5	2	FKM
O-Ring	26.57	33.63	3.53	FKM
O-Ring	26.64	31.88	2.62	FKM
O-Ring	26.7	30.26	1.78	FKM
O-Ring	27	30	1.5	FKM
O-Ring	27	31	2	FKM
O-Ring	27	32	2.5	FKM
O-Ring	27	33	3	FKM
O-Ring	27	34	3.5	FKM
O-Ring	27.3	32.1	2.4	FKM
O-Ring	27.5	31.5	2	FKM
O-Ring	27.94	38.6	5.33	FKM
O-Ring	28	31	1.5	FKM
O-Ring	28	32	2	FKM
O-Ring	28	33	2.5	FKM
O-Ring	28	34	3	FKM
O-Ring	28	35	3.5	FKM
O-Ring	28	36	4	FKM
O-Ring	28	38	5	FKM
O-Ring	28.17	35.23	3.53	FKM
O-Ring	28.24	33.48	2.62	FKM
O-Ring	28.3	31.86	1.78	FKM
O-Ring	28.5	32.5	2	FKM
O-Ring	29	32	1.5	FKM
O-Ring	29	33	2	FKM
O-Ring	29	34	2.5	FKM
O-Ring	29	35	3	FKM
O-Ring	29	36	3.5	FKM
O-Ring	29.4	35.6	3.1	FKM
O-Ring	29.5	33.5	2	FKM
O-Ring	29.5	35.5	3	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	29.51	40.17	5.33	FKM
O-Ring	29.74	36.8	3.53	FKM
O-Ring	29.82	35.06	2.62	FKM
O-Ring	29.87	33.43	1.78	FKM
O-Ring	30	33	1.5	FKM
O-Ring	30	34	2	FKM
O-Ring	30	35	2.5	FKM
O-Ring	30	36	3	FKM
O-Ring	30	37	3.5	FKM
O-Ring	30	38	4	FKM
O-Ring	30	40	5	FKM
O-Ring	31	35	2	FKM
O-Ring	31	36	2.5	FKM
O-Ring	31	37	3	FKM
O-Ring	31	38	3.5	FKM
O-Ring	31.12	41.78	5.33	FKM
O-Ring	31.34	38.4	3.53	FKM
O-Ring	31.42	36.66	2.62	FKM
O-Ring	31.47	35.03	1.78	FKM
O-Ring	32	35	1.5	FKM
O-Ring	32	36	2	FKM
O-Ring	32	37	2.5	FKM
O-Ring	32	38	3	FKM
O-Ring	32	39	3.5	FKM
O-Ring	32	40	4	FKM
O-Ring	32.69	43.35	5.33	FKM
O-Ring	32.92	39.98	3.53	FKM
O-Ring	32.92	39.98	3.53	FKM
O-Ring	32.99	38.23	2.62	FKM
O-Ring	33	38	2.5	FKM
O-Ring	33	39	3	FKM
O-Ring	33	41	4	FKM
O-Ring	33.05	36.61	1.78	FKM
O-Ring	33.3	38.1	2.4	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	33.3	38.1	2.4	FKM
O-Ring	34	38	2	FKM
O-Ring	34	39	2.5	FKM
O-Ring	34	40	3	FKM
O-Ring	34	41	3.5	FKM
O-Ring	34.29	44.95	5.33	FKM
O-Ring	34.52	41.58	3.53	FKM
O-Ring	34.59	39.83	2.62	FKM
O-Ring	34.65	38.21	1.78	FKM
O-Ring	35	39	2	FKM
O-Ring	35	40	2.5	FKM
O-Ring	35	41	3	FKM
O-Ring	35	42	3.5	FKM
O-Ring	35	43	4	FKM
O-Ring	35	45	5	FKM
O-Ring	36	40	2	FKM
O-Ring	36	41	2.5	FKM
O-Ring	36	42	3	FKM
O-Ring	36	44	4	FKM
O-Ring	36	46	5	FKM
O-Ring	36.09	43.15	3.53	FKM
O-Ring	36.17	41.41	2.62	FKM
O-Ring	36.5	42.5	3	FKM
O-Ring	37	40	1.5	FKM
O-Ring	37	41	2	FKM
O-Ring	37	44	3.5	FKM
O-Ring	37.4	41.4	2	FKM
O-Ring	37.46	48.12	5.33	FKM
O-Ring	37.69	44.75	3.53	FKM
O-Ring	37.69	44.75	3.53	FKM
O-Ring	37.82	41.38	1.78	FKM
O-Ring	38	41	1.5	FKM
O-Ring	38	42	2	FKM
O-Ring	38	43	2.5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	38	44	3	FKM
O-Ring	38	45	3.5	FKM
O-Ring	38	46	4	FKM
O-Ring	38	48	5	FKM
O-Ring	39	43	2	FKM
O-Ring	39	44	2.5	FKM
O-Ring	39	46	3.5	FKM
O-Ring	39.34	44.58	2.62	FKM
O-Ring	39.5	45.5	3	FKM
O-Ring	40	45	2.5	FKM
O-Ring	40	46	3	FKM
O-Ring	40	47	3.5	FKM
O-Ring	40	48	4	FKM
O-Ring	40	50	5	FKM
O-Ring	40.64	51.3	5.33	FKM
O-Ring	40.87	47.93	3.53	FKM
O-Ring	40.94	46.18	2.62	FKM
O-Ring	41	44.56	1.78	FKM
O-Ring	41	45	2	FKM
O-Ring	41	46	2.5	FKM
O-Ring	42	46	2	FKM
O-Ring	42	47	2.5	FKM
O-Ring	42	48	3	FKM
O-Ring	42	49	3.5	FKM
O-Ring	42	50	4	FKM
O-Ring	42	52	5	FKM
O-Ring	42.2	48.2	3	FKM
O-Ring	42.52	47.76	2.62	FKM
O-Ring	42.94	50	3.53	FKM
O-Ring	43	47	2	FKM
O-Ring	43	48	2.5	FKM
O-Ring	43	49	3	FKM
O-Ring	43.82	54.48	5.33	FKM
O-Ring	44	48	2	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	44	49	2.5	FKM
O-Ring	44	50	3	FKM
O-Ring	44	51	3.5	FKM
O-Ring	44.04	51.1	3.53	FKM
O-Ring	44.12	49.36	2.62	FKM
O-Ring	44.17	47.73	1.78	FKM
O-Ring	44.4	50.6	3.1	FKM
O-Ring	44.8	48.8	2	FKM
O-Ring	45	49	2	FKM
O-Ring	45	50	2.5	FKM
O-Ring	45	51	3	FKM
O-Ring	45	53	4	FKM
O-Ring	45	55	5	FKM
O-Ring	45.69	50.93	2.62	FKM
O-Ring	46	50	2	FKM
O-Ring	46	51	2.5	FKM
O-Ring	46	52	3	FKM
O-Ring	46	53	3.5	FKM
O-Ring	46	54	4	FKM
O-Ring	46.99	57.65	5.33	FKM
O-Ring	47	51	2	FKM
O-Ring	47	52	2.5	FKM
O-Ring	47	53	3	FKM
O-Ring	47.22	54.28	3.53	FKM
O-Ring	47.22	54.28	3.53	FKM
O-Ring	47.22	54.28	3.53	FKM
O-Ring	47.29	52.53	2.62	FKM
O-Ring	47.35	50.91	1.78	FKM
O-Ring	48	52	2	FKM
O-Ring	48	53	2.5	FKM
O-Ring	48	54	3	FKM
O-Ring	48	55	3.5	FKM
O-Ring	48	56	4	FKM
O-Ring	48	58	5	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	48.9	54.14	2.62	FKM
O-Ring	49	53	2	FKM
O-Ring	49	54	2.5	FKM
O-Ring	49	55	3	FKM
O-Ring	49	56	3.5	FKM
O-Ring	50	54	2	FKM
O-Ring	50	55	2.5	FKM
O-Ring	50	56	3	FKM
O-Ring	50	57	3.5	FKM
O-Ring	50	58	4	FKM
O-Ring	50	60	5	FKM
O-Ring	50.17	60.83	5.33	FKM
O-Ring	50.39	57.45	3.53	FKM
O-Ring	50.47	55.71	2.62	FKM
O-Ring	50.52	54.08	1.78	FKM
O-Ring	51	55	2	FKM
O-Ring	51	56	2.5	FKM
O-Ring	51	57	3	FKM
O-Ring	51	58	3.5	FKM
O-Ring	52	56	2	FKM
O-Ring	52	58	3	FKM
O-Ring	52	60	4	FKM
O-Ring	52.07	57.31	2.62	FKM
O-Ring	53	57	2	FKM
O-Ring	53	60	3.5	FKM
O-Ring	53	61	4	FKM
O-Ring	53.34	64	5.33	FKM
O-Ring	53.57	60.63	3.53	FKM
O-Ring	53.64	58.88	2.62	FKM
O-Ring	53.7	57.26	1.78	FKM
O-Ring	54	58	2	FKM
O-Ring	54	60	3	FKM
O-Ring	54	62	4	FKM
O-Ring	55	59	2	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	55	60	2.5	FKM
O-Ring	55	61	3	FKM
O-Ring	55	62	3.5	FKM
O-Ring	55	63	4	FKM
O-Ring	55	65	5	FKM
O-Ring	55	66	5.5	FKM
O-Ring	55.25	60.49	2.62	FKM
O-Ring	55.56	62.62	3.53	FKM
O-Ring	56	60	2	FKM
O-Ring	56	62	3	FKM
O-Ring	56	63	3.5	FKM
O-Ring	56	64	4	FKM
O-Ring	56.52	67.18	5.33	FKM
O-Ring	56.74	63.8	3.53	FKM
O-Ring	56.74	63.8	3.53	FKM
O-Ring	56.82	62.06	2.62	FKM
O-Ring	57	61	2	FKM
O-Ring	57	63	3	FKM
O-Ring	57	64	3.5	FKM
O-Ring	57	67	5	FKM
O-Ring	58	62	2	FKM
O-Ring	58	63	2.5	FKM
O-Ring	58	64	3	FKM
O-Ring	58	65	3.5	FKM
O-Ring	58	66	4	FKM
O-Ring	58.42	63.66	2.62	FKM
O-Ring	58.74	65.8	3.53	FKM
O-Ring	59	63	2	FKM
O-Ring	59	65	3	FKM
O-Ring	59.2	70.6	5.7	FKM
O-Ring	59.4	65.6	3.1	FKM
O-Ring	59.69	70.35	5.33	FKM
O-Ring	59.92	66.98	3.53	FKM
O-Ring	59.99	65.23	2.62	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	60	64	2	FKM
O-Ring	60	66	3	FKM
O-Ring	60	67.1	3.55	FKM
O-Ring	60	68	4	FKM
O-Ring	60	70	5	FKM
O-Ring	60.05	63.61	1.78	FKM
O-Ring	61	65	2	FKM
O-Ring	61	67	3	FKM
O-Ring	61	71	5	FKM
O-Ring	61.6	66.84	2.62	FKM
O-Ring	62	66	2	FKM
O-Ring	62	68	3	FKM
O-Ring	62	70	4	FKM
O-Ring	62.87	73.53	5.33	FKM
O-Ring	63	67	2	FKM
O-Ring	63	69	3	FKM
O-Ring	63	71	4	FKM
O-Ring	63.09	70.15	3.53	FKM
O-Ring	63.22	66.78	1.78	FKM
O-Ring	64	68	2	FKM
O-Ring	64	70	3	FKM
O-Ring	64	71	3.5	FKM
O-Ring	64.77	70.01	2.62	FKM
O-Ring	65	69	2	FKM
O-Ring	65	71	3	FKM
O-Ring	65	72	3.5	FKM
O-Ring	65	73	4	FKM
O-Ring	65	75	5	FKM
O-Ring	66	70	2	FKM
O-Ring	66	71	2.5	FKM
O-Ring	66	72	3	FKM
O-Ring	66.04	76.7	5.33	FKM
O-Ring	66.27	73.33	3.53	FKM
O-Ring	66.34	71.58	2.62	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	66.4	69.96	1.78	FKM
O-Ring	67	73	3	FKM
O-Ring	67.95	73.19	2.62	FKM
O-Ring	68	72	2	FKM
O-Ring	68	74	3	FKM
O-Ring	68	75	3.5	FKM
O-Ring	69	73	2	FKM
O-Ring	69	75	3	FKM
O-Ring	69	76	3.5	FKM
O-Ring	69.22	79.88	5.33	FKM
O-Ring	69.44	76.5	3.53	FKM
O-Ring	69.44	76.5	3.53	FKM
O-Ring	69.52	74.76	2.62	FKM
O-Ring	69.57	73.13	1.78	FKM
O-Ring	70	74	2	FKM
O-Ring	70	76	3	FKM
O-Ring	70	77	3.5	FKM
O-Ring	70	78	4	FKM
O-Ring	70	80	5	FKM
O-Ring	71.12	76.36	2.62	FKM
O-Ring	72	76	2	FKM
O-Ring	72	78	3	FKM
O-Ring	72	80	4	FKM
O-Ring	72.39	83.05	5.33	FKM
O-Ring	72.62	79.68	3.53	FKM
O-Ring	72.69	77.93	2.62	FKM
O-Ring	72.75	76.31	1.78	FKM
O-Ring	73	79	3	FKM
O-Ring	73	80	3.5	FKM
O-Ring	74	80	3	FKM
O-Ring	74	81	3.5	FKM
O-Ring	74	82	4	FKM
O-Ring	74	84	5	FKM
O-Ring	75	79	2	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	75	80	2.5	FKM
O-Ring	75	81	3	FKM
O-Ring	75	83	4	FKM
O-Ring	75	85	5	FKM
O-Ring	75.57	86.23	5.33	FKM
O-Ring	75.79	82.85	3.53	FKM
O-Ring	75.87	81.11	2.62	FKM
O-Ring	75.92	79.48	1.78	FKM
O-Ring	76	80	2	FKM
O-Ring	76	82	3	FKM
O-Ring	78	84	3	FKM
O-Ring	78	86	4	FKM
O-Ring	78.74	89.4	5.33	FKM
O-Ring	78.97	86.03	3.53	FKM
O-Ring	79.5	85.5	3	FKM
O-Ring	80	84	2	FKM
O-Ring	80	86	3	FKM
O-Ring	80	88	4	FKM
O-Ring	80	90	5	FKM
O-Ring	81.92	92.58	5.33	FKM
O-Ring	82	90	4	FKM
O-Ring	82.14	89.2	3.53	FKM
O-Ring	82.22	87.46	2.62	FKM
O-Ring	82.27	85.83	1.78	FKM
O-Ring	83	89	3	FKM
O-Ring	84	90	3	FKM
O-Ring	84.5	90.5	3	FKM
O-Ring	85	91	3	FKM
O-Ring	85	93	4	FKM
O-Ring	85	95	5	FKM
O-Ring	85.09	95.75	5.33	FKM
O-Ring	85.32	92.38	3.53	FKM
O-Ring	85.32	92.38	3.53	FKM
O-Ring	86	92	3	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	88	94	3	FKM
O-Ring	88.27	98.93	5.33	FKM
O-Ring	88.57	93.81	2.62	FKM
O-Ring	89	95	3	FKM
O-Ring	89	99	5	FKM
O-Ring	90	94	2	FKM
O-Ring	90	95	2.5	FKM
O-Ring	90	96	3	FKM
O-Ring	90	97	3.5	FKM
O-Ring	90	98	4	FKM
O-Ring	90	100	5	FKM
O-Ring	91.44	102.1	5.33	FKM
O-Ring	91.67	98.73	3.53	FKM
O-Ring	92	100	4	FKM
O-Ring	94	100	3	FKM
O-Ring	94	102	4	FKM
O-Ring	94.62	105.28	5.33	FKM
O-Ring	94.84	101.9	3.53	FKM
O-Ring	94.92	100.16	2.62	FKM
O-Ring	95	101	3	FKM
O-Ring	95	103	4	FKM
O-Ring	95	105	5	FKM
O-Ring	95	106	5.5	FKM
O-Ring	96	102	3	FKM
O-Ring	96	103	3.5	FKM
O-Ring	97.79	108.45	5.33	FKM
O-Ring	98	104	3	FKM
O-Ring	98.02	105.08	3.53	FKM
O-Ring	100	105	2.5	FKM
O-Ring	100	106	3	FKM
O-Ring	100	108	4	FKM
O-Ring	100	110	5	FKM
O-Ring	100.97	111.63	5.33	FKM
O-Ring	101.19	108.25	3.53	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	101.27	106.51	2.62	FKM
O-Ring	102	108	3	FKM
O-Ring	104	110	3	FKM
O-Ring	104.14	114.8	5.33	FKM
O-Ring	104.37	111.43	3.53	FKM
O-Ring	105	111	3	FKM
O-Ring	105	113	4	FKM
O-Ring	105	115	5	FKM
O-Ring	105	116	5.5	FKM
O-Ring	107.32	117.98	5.33	FKM
O-Ring	107.54	114.6	3.53	FKM
O-Ring	107.62	112.86	2.62	FKM
O-Ring	108	114	3	FKM
O-Ring	110	116	3	FKM
O-Ring	110	117	3.5	FKM
O-Ring	110	118	4	FKM
O-Ring	110	120	5	FKM
O-Ring	110.49	121.15	5.33	FKM
O-Ring	110.72	117.78	3.53	FKM
O-Ring	112	118	3	FKM
O-Ring	113.67	124.33	5.33	FKM
O-Ring	113.67	127.65	6.99	FKM
O-Ring	113.89	120.95	3.53	FKM
O-Ring	113.97	119.21	2.62	FKM
O-Ring	115	121	3	FKM
O-Ring	115	125	5	FKM
O-Ring	116.84	127.5	5.33	FKM
O-Ring	116.84	130.82	6.99	FKM
O-Ring	117.07	124.13	3.53	FKM
O-Ring	118	124	3	FKM
O-Ring	118	125	3.5	FKM
O-Ring	118	128	5	FKM
O-Ring	120	126	3	FKM
O-Ring	120	128	4	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	120	130	5	FKM
O-Ring	120.02	130.68	5.33	FKM
O-Ring	120.02	134	6.99	FKM
O-Ring	120.24	127.3	3.53	FKM
O-Ring	120.32	125.56	2.62	FKM
O-Ring	122	130	4	FKM
O-Ring	123.19	133.85	5.33	FKM
O-Ring	123.19	137.17	6.99	FKM
O-Ring	123.42	130.48	3.53	FKM
O-Ring	125	131	3	FKM
O-Ring	125	132	3.5	FKM
O-Ring	125	135	5	FKM
O-Ring	126.37	137.03	5.33	FKM
O-Ring	126.37	140.35	6.99	FKM
O-Ring	126.59	133.65	3.53	FKM
O-Ring	126.67	131.91	2.62	FKM
O-Ring	127	133	3	FKM
O-Ring	128	134	3	FKM
O-Ring	129.54	140.2	5.33	FKM
O-Ring	129.54	143.52	6.99	FKM
O-Ring	129.77	136.83	3.53	FKM
O-Ring	130	135	2.5	FKM
O-Ring	130	136	3	FKM
O-Ring	130	138	4	FKM
O-Ring	130	140	5	FKM
O-Ring	132.72	143.38	5.33	FKM
O-Ring	132.72	146.7	6.99	FKM
O-Ring	132.94	140	3.53	FKM
O-Ring	134.5	140.5	3	FKM
O-Ring	135	145	5	FKM
O-Ring	135.89	146.55	5.33	FKM
O-Ring	135.89	149.87	6.99	FKM
O-Ring	136.12	143.18	3.53	FKM
O-Ring	139.07	149.73	5.33	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	139.29	146.35	3.53	FKM
O-Ring	139.37	144.61	2.62	FKM
O-Ring	140	146	3	FKM
O-Ring	140	150	5	FKM
O-Ring	140	154	7	FKM
O-Ring	142.24	152.9	5.33	FKM
O-Ring	142.24	156.22	6.99	FKM
O-Ring	142.47	149.53	3.53	FKM
O-Ring	144	158	7	FKM
O-Ring	145.42	156.08	5.33	FKM
O-Ring	145.64	152.7	3.53	FKM
O-Ring	145.72	150.96	2.62	FKM
O-Ring	148.59	159.25	5.33	FKM
O-Ring	148.59	162.57	6.99	FKM
O-Ring	148.82	155.88	3.53	FKM
O-Ring	150	158	4	FKM
O-Ring	150	160	5	FKM
O-Ring	150	162	6	FKM
O-Ring	151.77	162.43	5.33	FKM
O-Ring	151.77	165.75	6.99	FKM
O-Ring	151.99	159.05	3.53	FKM
O-Ring	152	162	5	FKM
O-Ring	158.12	172.1	6.99	FKM
O-Ring	158.34	165.4	3.53	FKM
O-Ring	159.3	170.7	5.7	FKM
O-Ring	160	166	3	FKM
O-Ring	160	170	5	FKM
O-Ring	164.47	175.13	5.33	FKM
O-Ring	164.69	171.75	3.53	FKM
O-Ring	165	171	3	FKM
O-Ring	165	175	5	FKM
O-Ring	170	180	5	FKM
O-Ring	170.82	181.48	5.33	FKM
O-Ring	171.04	178.1	3.53	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	175	181	3	FKM
O-Ring	175	183	4	FKM
O-Ring	177.17	187.83	5.33	FKM
O-Ring	177.39	184.45	3.53	FKM
O-Ring	179.3	190.7	5.7	FKM
O-Ring	180	188	4	FKM
O-Ring	180	190	5	FKM
O-Ring	183.52	194.18	5.33	FKM
O-Ring	183.74	190.8	3.53	FKM
O-Ring	185	191	3	FKM
O-Ring	189.87	200.53	5.33	FKM
O-Ring	190	200	5	FKM
O-Ring	190.09	197.15	3.53	FKM
O-Ring	195	205	5	FKM
O-Ring	196.22	206.88	5.33	FKM
O-Ring	196.44	203.5	3.53	FKM
O-Ring	200	206	3	FKM
O-Ring	200	210	5	FKM
O-Ring	202.57	213.23	5.33	FKM
O-Ring	202.79	209.85	3.53	FKM
O-Ring	205	215	5	FKM
O-Ring	208.92	219.58	5.33	FKM
O-Ring	209.14	216.2	3.53	FKM
O-Ring	210	218	4	FKM
O-Ring	215.49	222.55	3.53	FKM
O-Ring	220	226	3	FKM
O-Ring	220	230	5	FKM
O-Ring	221.62	232.28	5.33	FKM
O-Ring	227.97	238.63	5.33	FKM
O-Ring	228.19	235.25	3.53	FKM
O-Ring	230	236	3	FKM
O-Ring	230	238	4	FKM
O-Ring	230	240	5	FKM
O-Ring	234.32	244.98	5.33	FKM

O-RING



Profile	ID	OD	THK	Material
O-Ring	240	248	4	FKM
O-Ring	240	250	5	FKM
O-Ring	240.67	251.33	5.33	FKM
O-Ring	240.67	254.65	6.99	FKM
O-Ring	240.89	247.95	3.53	FKM
O-Ring	240.97	246.21	2.62	FKM
O-Ring	247.02	257.68	5.33	FKM
O-Ring	253.59	260.65	3.53	FKM
O-Ring	260	270	5	FKM
O-Ring	266.07	276.73	5.33	FKM
O-Ring	266.29	273.35	3.53	FKM
O-Ring	278.99	286.05	3.53	FKM
O-Ring	304.17	314.83	5.33	FKM
O-Ring	304.39	311.45	3.53	FKM
O-Ring	329.57	340.23	5.33	FKM
O-Ring	329.79	336.85	3.53	FKM
O-Ring	380.37	391.03	5.33	FKM
O-Ring	380.59	387.65	3.53	FKM
O-Ring	456.06	466.72	5.33	FKM